

Product Search

Your Search for "nys" returned **72** Match(es):

Patch Panels



NYS-SPP-L 1/4 Jacks



For NYS connector products please refer to www.rean-connector.com



NYS-SPP-L

1/4" Patch Panel with 2 rows of sockets, 24 front pairs and 24 rear pairs. 19" rack-mount and fully PCB-wired (24 vertical PC boards) without nut fastening. Identification strips incl. for front and rear panel.

Technical Data:

Electrical

Connector-contact resistance: < 10 mOhm
Switch-contact resistance: < 10 Ohm
Insulation resistance: > 2G Ohm @ 500 V dc

Current rating: 1 A

Dielectric strength: > 1000 V dc

Crosstalk between upper and lower channel: > 100 dB @ 1 kHz

Mechanical

Jack lifetime: > 10.000 insertions/withdrawal cycles

Dimensions: 483 mm (W) x 44 mm (H) x 71 mm (D)

Insertion/withdrawal force: < 20 N / > 10 N

Rack mount panel: 19" x 1U

Materials

Housing: Steel, black coated

Connector shell: ABS

Contacts: CuZn39Pb3, CuSn6 plated

Temperature range: -30°C to +80°C

[Specs](#) [PDF](#) [DXF](#)



Larger Font



Smaller Font



Print



Send Link



Back

NYS Product Range

1/4" Plugs

NYS201

1/4" plug, 2-pole, short turned brass handle.

[Specs](#) [PDF](#) [DXF](#)

NYS202

1/4" plug, 3-pole, short turned brass handle.

[Specs](#) [PDF](#) [DXF](#)



NYS203

¼" plug, 2-pole, plastic handle with flexible strain relief.

[Specs](#) [PDF](#) [DXF](#)

NYS204

¼" plug, 3-pole, plastic handle with flexible strain relief.

[Specs](#) [PDF](#) [DXF](#)

NYS207

¼" plug right angle, 2-pole, metal housing and plastic bushing.

[Specs](#) [PDF](#) [DXF](#)

NYS208

¼" plug right angle, 3-pole, metal housing and plastic bushing.

[Specs](#) [PDF](#) [DXF](#)

NYS224

¼" plug, 2-pole, long turned brass handle, no rivet.

[Specs](#) [PDF](#) [DXF](#)

NYS224AG

¼" plug, 2-pole, long turned brass handle, no rivet. With gold plated shell and contacts.

[Specs](#) [PDF](#) [DXF](#)

NYS224G

¼" plug, 2-pole, long turned brass handle, no rivet. With gold plated contacts.

[Specs](#) [PDF](#) [DXF](#)

NYS224GT

¼" plug, 2-pole, long turned brass handle, no rivet. With gold plated tip contact.

[Specs](#) [PDF](#) [DXF](#)

NYS224L

¼" plug, 2-pole, long turned brass handle, no rivet. With large cable outlet of 8 mm.

[Specs](#) [PDF](#) [DXF](#)

NYS224S

¼" plug, 2-pole, long turned brass handle, no rivet. With tip switched to ground if not inserted (silent).

[Specs](#) [PDF](#) [DXF](#)

**NYS225**

¼" plug, 2-pole, with large shell for speaker cable. Large metal handle, rubber bushing.

[Specs](#) [PDF](#) [DXF](#)

**NYS225B**

¼" plug, 2-pole, with large shell for speaker cable. With black plated metal handle.

[Specs](#) [PDF](#) [DXF](#)

**NYS225L**

¼" plug, 2-pole, with large shell for speaker cable. With large cable outlet.

[Specs](#) [PDF](#) [DXF](#)

**NYS225S**

¼" plug, 2-pole, with large shell for speaker cable. With tip switched to ground if not inserted (silent).

[Specs](#) [PDF](#) [DXF](#)

**NYS228**

¼" plug, 3-pole, long turned brass handle, no rivet. Stereo version of 224.

[Specs](#) [PDF](#) [DXF](#)

**NYS228BG**

¼" plug, 3-pole, long turned brass handle, no rivet. With black handle, gold plated contacts.

[Specs](#) [PDF](#) [DXF](#)

**NYS237**

¼" plug adapter to mate standard ¼" jacks, full metal, 2-pole.

[Specs](#) [PDF](#) [DXF](#)

**NYS239**

¼" plug adapter to mate standard ¼" jacks, full metal, 3-pole.

[Specs](#) [PDF](#) [DXF](#)

**3.5 mm Plugs****NYS226**

3.5 mm plug, 2-pole, metal handle with crimp strain relief.

[Specs](#) [PDF](#) [DXF](#)

**NYS226BG**

3.5 mm plug, 2-pole, black metal handle, gold plated contacts.

[Specs](#) [PDF](#) [DXF](#)

[Specs](#) [PDF](#) [DXF](#)

NYS227

3.5 mm plug to ¼" stereo jack, all metal, 3-pole.

[Specs](#) [PDF](#) [DXF](#)

NYS231

3.5 mm plug, 3-pole, metal housing with crimp strain relief.

[Specs](#) [PDF](#) [DXF](#)

NYS231B

3.5 mm plug, 3-pole, black metal handle.

[Specs](#) [PDF](#) [DXF](#)

NYS231BG

3.5 mm plug, 3-pole, black metal handle, gold plated contacts.

[Specs](#) [PDF](#) [DXF](#)

NYS231G

3.5 mm plug, 3-pole, metal handle, gold plated contacts.

[Specs](#) [PDF](#) [DXF](#)

NYS231L

3.5 mm plug, 3-pole, metal handle, large cable outlet.

[Specs](#) [PDF](#) [DXF](#)

Jacks

NYS212

Horizontal jack (all contacts switched), 3-pole, plastic housing with nut and washer, solder tap version.

[Specs](#) [PDF](#) [DXF](#)

NYS2122

Horizontal jack (all contacts switched), 2-pole, solder tap version.

[Specs](#) [PDF](#) [DXF](#)

NYS215

Horizontal jack (all contacts switched), 3-pole, with chrome ferrule nut.

[Specs](#) [PDF](#) [DXF](#)

**NYS2152**

Horizontal jack (all contacts switched), 2-pole, with chrome ferrule nut.

[Specs](#) [PDF](#) [DXF](#)

**NYS216**

Horizontal jack (all contacts switched), 3-pole, plastic housing with nut and washer.

[Specs](#) [PDF](#) [DXF](#)

**NYS2162**

Horizontal jack (all contacts switched), 2-pole, plastic housing with nut and washer.

[Specs](#) [PDF](#) [DXF](#)

**NYS216G**

Horizontal jack (all contacts switched), 3-pole, plastic housing with nut and washer, gold contacts.

[Specs](#) [PDF](#) [DXF](#)

**NYS218**

Horizontal jack (all contacts switched), 3-pole, with extra long contacts.

[Specs](#) [PDF](#) [DXF](#)

**NYS2182**

Horizontal jack (all contacts switched), 2-pole, with extra long contacts.

[Specs](#) [PDF](#) [DXF](#)

**NYS219**

Horizontal jack (all contacts switched), 3-pole, with longer contacts.

[Specs](#) [PDF](#) [DXF](#)

**NYS2192**

Horizontal jack (all contacts switched), 2-pole, with longer contacts.

[Specs](#) [PDF](#) [DXF](#)

**NYS2202**

Jack for thick panels, 2-pole, long-threaded bushing with washer and nut, full metal.

[Specs](#) [PDF](#) [DXF](#)

**NYS2203**

Jack for thick panels, 3-pole, long-threaded bushing with washer and nut, full metal.

[Specs](#) [PDF](#) [DXF](#)

**NYS221**

Jack with special designed head for guitar strap, for thick panels, 3-pole, long-threaded bushing with washer and nut, full metal.

pole, long-threaded bushing with washer and nut, full metal.

[Specs](#) [PDF](#) [DXF](#)

NYS229

Open jack, 2-pole, 2 contacts, with washer and nut, panel thickness 3.5 mm.

[Specs](#) [PDF](#) [DXF](#)

NYS229L

Open jack, 2-pole, 2 contacts, with longer threaded nose, washer and nut, panel thickness 6.5 mm, with 0.205" faston tabs.

[Specs](#) [PDF](#) [DXF](#)

NYS230

Open jack, 3-pole, 3 contacts, with washer and nut, panel thickness 3.5 mm.

[Specs](#) [PDF](#) [DXF](#)

NYS232

Vertical jack, plastic housing, 3-pole, metal washer and nut, with tip and ring normalling contacts.

[Specs](#) [PDF](#) [DXF](#)

NYS234

Vertical jack, plastic housing, 3-pole, metal washer and nut, with tip and ring normalling contacts.

[Specs](#) [PDF](#) [DXF](#)

NYS2343

Vertical jack, plastic housing, 3-pole, metal washer and nut, no normalling contacts.

[Specs](#) [PDF](#) [DXF](#)

NYS236

¼" phone jack adapter to mate with standard ¼" plug, full metal, 2-pole.

[Specs](#) [PDF](#) [DXF](#)

NYS238

¼" phone jack adapter to mate with standard ¼" plug, full metal, 3-pole.

[Specs](#) [PDF](#) [DXF](#)

Phono (RCA) Plugs

NYS352

Phono plug, cable O.D. 7.2 mm.

[Specs](#) [PDF](#) [DXF](#)

**NYS352AG**

Phono plug, all gold plated.

[Specs](#) [PDF](#) [DXF](#)**NYS352BG**

Phono plug with gold plated contacts and black plated handle.

[Specs](#) [PDF](#) [DXF](#)**NYS352G**

Phono plug with gold plated contacts.

[Specs](#) [PDF](#) [DXF](#)**NYS354**

Phono receptacle, PCB-mount, max. panel thickness 1.2 mm.

[Specs](#) [PDF](#) [DXF](#)**NYS355**

Phono to phono female adapter.

[Specs](#) [PDF](#) [DXF](#)**NYS367-***

Phono chassis mount socket, gold plated contacts, color coding.

*: 0-Black, 2-Red, 4-Yellow, 5-Green, 6-Blue, 9-White

[Specs](#) [PDF](#) [DXF](#)**NYS373-***

Phono plug with gold plated contacts, black chromium shell, chuck type strain relief, cable O.D. 3.0 - 6.1 mm, color marking ring.

*: 0-Black, 2-Red, 4-Yellow, 5-Green, 6-Blue, 9-White

[Specs](#) [PDF](#) [DXF](#)**DIN Connectors****NYS321**

DIN male cable connector, 3-pole, silver plated contacts.

[Specs](#) [PDF](#) [DXF](#)**NYS321G**

DIN male cable connector, 3-pole, gold plated contacts.

[Specs](#) [PDF](#) [DXF](#)**NYS322**

DIN male cable connector, 5-pole, silver plated contacts.

[Specs](#) [PDF](#) [DXF](#)

[Specs](#) [PDF](#) [DXF](#)

NYS322AG

DIN male cable connector, 5-pole, gold plated shell and contacts.

[Specs](#) [PDF](#) [DXF](#)

NYS322G

DIN male cable connector, 5-pole, gold plated contacts.

[Specs](#) [PDF](#) [DXF](#)

NYS323

DIN male cable connector, 7-pole, silver plated contacts.

[Specs](#) [PDF](#) [DXF](#)

NYS323G

DIN male cable connector, 7-pole, gold plated contacts.

[Specs](#) [PDF](#) [DXF](#)

NYS324

DIN female chassis connector, 3-pole, silver plated contacts.

[Specs](#) [PDF](#) [DXF](#)

NYS325

DIN female chassis connector, 5-pole, silver plated contacts.

[Specs](#) [PDF](#) [DXF](#)

NYS326

DIN female chassis connector, 7-pole, silver plated contacts.

[Specs](#) [PDF](#) [DXF](#)

Patch Panels

NYS-SPCR

Send/return module (split print). To be built into the NYS-SPP-L.

[Specs](#) [PDF](#) [DXF](#)

NYS-SPP-L

¼" Patch Panel with 2 rows of sockets, 24 front pairs and 24 rear pairs. Fully PCB-wired without nut fastening. Identification strips incl. for front and rear panel.

[Specs](#) [PDF](#) [DXF](#)



Stage Box



NYS-SSR8

¼" Patch Box with 8 Send/Return Moduls (Split Print).

[Specs](#) [PDF](#) [DXF](#)

