

rotronic

Datenblatt - Fiche technique - Data sheet


11.99.8961




VALUE USB 2.0 Kabel, Typ A-A, ST/BU, 3,0m

VALUE Câble USB 2.0 Type A-A, M/F, 3.0m

VALUE USB 2.0 Cable, Type A-A, M/F, 3 m



PIN OUT



NOTE 1:

ITEM NO.	LENGTH
11. 99. 8946R	800 ± 20mm
11. 99. 8949R	1800 ± 30mm
11. 99. 8961R	3000 ± 50mm

NOTE:

- Electrical test:
 - 100% open short & miss wire test;
 - Insulation resistance:DC 300V 10M Ω ;
 - Contact resistance:5Ω Max;
 - Dielectric strength:100V AC/Minute, 1mA.
- RoHS compliant
- PRINTING:USB 2.0 CABLE, 28AWG×1P+28AWG×2C
- Packing: 1PCS/PE BAG + LABEL 100PCS/CARTON

MATERIAL LIST:

④	OUTER MOLD	Shore 88A PVC(UL94V-2)color For White	2	
③	USB A TYPE	USB A /F Type, The Pin Gold Plating 30u", the shell for Nickel Plating	1	
②	USB A TYPE	USB A /M Type, The Pin Gold Plating 30u", the shell for Nickel Plating	1	
①	CABLE	USB 2.0 28AWG(7/0.12BC*1P)+28AWG(7/0.12BC*2C)+AEB B=0.12/3*16 AL-MG E=7/0.12BC JACKET:PVC/WHITE (WH11) OD: 3.8±0.2mm	1	
NO.	PARTS NAME	SPECIFICATION STANDARD	QT' Y	REMARK

Rotonic Co., Ltd

		REF.	ITEM NO.	11. 99. 8946	11. 99. 8961
				11. 99. 8949	
		PRODUCT NAME	USB 2.0 AM/AF	DRAW NO.	UNTT MM
		DRAWNBY	CHECKBY	APPOBY	DATE
BY	CHK	REVISION RECORD MODIFICATIONS	DATE	REV.	2009-11-20