




Datenblatt - Fiche technique - Data sheet


11.02.8908



ROLINE USB 2.0 Kabel, Typ A-A, 0,8m

ROLINE Câble USB 2.0 Type A-A, 0,8m

ROLINE USB 2.0 Cable, A - A, M/M, 0.8 m



JACKET PRINTING:USB SHIELDED HIGH SPEED CABLE 2.0 REVISION
 28AWG/1P+24AWG/2C E314459 兪 AWM 2725 80℃ 30V VW-1

NOTE:


1. CABLE: UL2725,AL+B-FOIL,28AWG*1P+24AWG*2C,BLACK COLOR,OD=5.0mm,PVC JACKET.
 (AL/MG 65%,double shielded, bare copper conductor,)(NOTE: USB2.0 WIRE MATERIAL).

2. LENGHT: 800mm.
3. CONNECTORS:USBM(A)*2PCS(WHITE INSULATOR)(SHELL NICKEL)(PIN GOLD FLASH 30U”).
4. MOLD:MOLDING USBAM TYPE.
5. CONTACTS:

1	2	3	4	64
1	2	3	4	64

1	2	3	4	64
RED	WHITE	GREEN	BLACK	SHIELD
#28 #28 PAIR				

- WHITE/GREEN PAIR...28AWG , RED/BLACK...24AWG
6. OPEN/SHORT TEST: 100% TEST.
 - A.100% OPEN,SHORT&INTERMITTANCE TEST.
 - B.CONDUCTOR RESISTANCE: 3ohms MAX.
 - C.INSULATION RESISTANCE: 5M Min/,10ms:
 7. ALL MUST BE ROHS COMPLIANT.



PE BAG(100*200*0.06)ROLINE HEADER+EAN STICKER

COMPANY	RLA	ITEM NO.	11.02.8908	NO	B4647	Parts Name	USBAM-USBAM
---------	-----	----------	------------	----	-------	------------	-------------

REVISION	DATE	DISCRIPTION
----------	------	-------------

REV.A/0	2012.05.08	
---------	------------	--

DRAWN BY	DESIGNED BY	APPROVAL BY
----------	-------------	-------------

SPEC

Rotronic Co.,Ltd.

SCALE	NDN
-------	-----

UNIT(mm)	
----------	--

PAGE	
------	--