



Datenblatt - Fiche technique - Data sheet


**12.03.3110**



ROLINE DVI-VGA Adapter, DVI BU / VGA ST

ROLINE Adaptateur DVI F / VGA M

ROLINE DVI-VGA Adapter, DVI F - HD15 M



包装方式: 真空罩+插卡包装+条码贴纸

NOTE:

- CABLE: (A)30AWG, NON-UL, NON-FOIL, (#30\*1C+B+PVC)\*3PCS, OD=2.5mm, PVC JACKET  
 (B)28AWG, UL1007, NON-FOIL, WIRE, BLACK COLOR\*5PCS, PVC JACKET  
 (C)28AWG, UL1007, NON-FOIL, WIRE, BLACK/RED PAIR, PVC JACKET

2. LENGTH: 55mm

3. CONNECTORS: DVI29(F)\* 1--HDB15M\*1(BLACK INSULATOR)

4. MOLD: 成型转换头模(黑色)

5. CONTACTS:

DVI29(F)	6	7	C1	C5	C2	C5	C3	C5	8	14+16	15	C4	64
HD15M	15	12	1	6+7+8	2	6+7+8	3	6+7+8	14	9	5+10	13	64
	对绞		红轴	红地	绿轴	绿地	蓝轴	蓝轴	28AWG				

6. OPEN/SHORT TEST: 100% TEST.  
 INSULATION: MIN. 2M.

COMPANY	RLA		ITEM NO.	12.03.3110	NO	B3874	Rotronic Co., Ltd.	SCALE	
REVISION	DATE	DISCRIPTION	DRAWN BY					UNIT(mm)	
REV.A/0	2006.04.28	C9-2604034	DESIGNED BY					DRAWING NO.	
REV.A/1	2006.05.19	增加包装方式	APPROVAL BY						