





**4-CONDUCTOR MINIATURE EARTH
CONDUCTOR TERMINAL BLOCK
CENTRE MARKING for DIN 15 rail
264-727**

| | |
|--|------------|
| ITEM-NO. (ITEM-NO.) | 264-727 |
| Cross section1 (Cross section / mm²) | 0.08 - 2.5 |
| Cross section2 (Cross section / AWG) | 28 - 12 |
| Strip length (Strip length / mm) | 8 - 9 |
| Height (Height / mm) | 24.5 |
| Width (Width / mm) | 10 |
| Depth (Depth / mm) | 32 |
| No. of connection Points (No. of connection Points) | 4 |
| No. of potentials (No. of potentials) | 1 |
| COLOR (COLOR) | grün-gelb |
| WEIGHT (WEIGHT / g) | 7.5 |
| Comment (Comment) | |