


**4-CONDUCTOR DEVICE
CONNECTORS FOR FIXING SCREW
AND NUT 3 MM Ø OR FOR SELF
TAPPING SREW 2.9 MM Ø FROM TOP**



**4-CONDUCTOR DEVICE
CONNECTORS FOR FIXING SCREW
AND NUT 3 MM Ø OR FOR SELF
TAPPING SREW 2.9 MM Ø FROM TOP
4 POLE
862-504 TO 862-2604**

ITEM-NO. (ITEM-NO.)	862-504
Cross section1 (Cross section / mm²)	0.5 - 4
Cross section2 (Cross section / AWG)	20 - 12
Strip length (Strip length / mm)	10 - 11
Measured voltage (Measured voltage / V)	500
Measured shock voltage (Measured shock voltage / kV)	6
Pollution degree (Pollution degree)	3
Current intensity (Current intensity / A)	32
P (NO. OF POLES)	4
Height (Height / mm)	21.4
Width (Width / mm)	48
Depth (Depth / mm)	35
No. of connection Points (No. of connection Points)	16
No. of potentials (No. of potentials)	4
COLOR (COLOR)	schwarz
Comment (Comment)	ohne Aufdruck