



THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	09/13/17	D.FRISIELLO



WIRING DIAGRAM



MODEL NUMBER	LENGTH		
	METERS	FEET	TOL. (IN)
U3A00056-03M	0.3	0.98	+/- 1.18
U3A00056-05M	0.5	1.64	+/- 1.18
U3A00056-1M	1.0	3.28	+/- 1.18
U3A00056-2M	2.0	6.56	+/- 1.97
U3A00056-3M	3.0	9.84	+/- 1.97

NOTES

- ELECTRICAL:  
 VOLTAGE TEST: DC 300V 10ms  
 INSULATION RESISTANCE: 10.0M Ω, MIN  
 CONDUCTANCE RESISTANCE: 5.0 Ω, MAX.
- MOUNTING HARDWARE INCLUDED: 2X #4-40 SCREW
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

REGULATORY COMPLIANCE:  
 CE2011/65/EU (RoHS DIRECTIVE)

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0%	APPROVALS	DATE	 50 HIGH STREET NORTH ANDOVER, MA 01845	
	DRAWN BY D.CUI	09/13/17		
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5.08] .XX = ± .02 [51] .XXX = ±.005 [1.27]	CHECKED BY D.FRISIELLO	09/13/17	PRODUCT DESCRIPTION	
	APPROVED BY B.GATES	09/13/17	CA USB-C PNL/USB-CM	
PROJECTION	COLOR VARIATIONS MAY OCCUR	SIZE <b>A</b>	FSCM NO. <b>43321</b>	DWG. NO. <b>U3A00056</b>
		SCALE: NONE	CAD FILE: U3A00056.SLDDRW	SHEET 1 OF 1