


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	INITIAL RELEASE	11/27/2019	GUTTADAURO




USB 3.0
SERIES A PLUG
MOLDED, BLACK

UL STYLE 21445
2X PARALLEL PAIR 26AWG STRANDED TINNED COPPER
WITH INDIVIDUAL CU/MYLAR TAPE AND BRAIDED SHIELDS
1X UTP 28AWG STRANDED TINNED COPPER
2 CONDUCTOR 22AWG STRANDED TINNED COPPER
WITH OVERALL PLASTIC TAPE AND TINNED COPPER BRAIDED SHIELD
JACKET: TPE, VW-1, VIOLET (NOM.. DIA. 8.0[.315])

USB 3.0
SERIES MICRO-B PLUG
MOLDED, BLACK



WIRING DIAGRAM



MODEL NUMBER	LENGTH (±50mm) METER [FEET]
CAU3VISHFAMB-1M	1 [3.28]
CAU3VISHFAMB-2M	2 [6.56]
CAU3VISHFAMB-3M	3 [9.84]

NOTES:

- HIGH FLEX CABLE RATING: 1 MILLION CYCLES MIN.
- CABLE ASSEMBLY SHALL MEET USB 3.0 REQUIREMENTS.
- CABLE ASSEMBLY SHALL BE TESTED FOR CONTINUITY.
- CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH L-COM SPECIFICATION PS-0031.

UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm]	APPROVALS	DATE	 an INFINITO brand	50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936		
	OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0	DRAWN BY BPUCHASKI			11/27/2019	
ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13]	CHECKED BY DFRISIELLO	11/27/2019	CATEGORY USB			
	APPROVED BY GUTTADAURO	11/27/2019	PRODUCT DESCRIPTION USB 3.0 A/MicB VISION HIGHFLEX			
THIRD-ANGLE PROJECTION 	CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY	COLOR VARIATIONS MAY OCCUR	SIZE A	CAGE CODE 43321	DWG. NO. CAU3VISHFAMB	REV. A
SCALE: NONE			CAD FILE: CAU3VISHFAMB.SLDRW	SHEET 1 OF 1		