


THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF AMPHENOL INTERCONNECT PRODUCTS CORP. ANY REPRODUCTION OR DISCLOSURE TO THIRD PARTIES, IN PART OR WHOLE, WITHOUT THE EXPRESS WRITTEN PERMISSION OF AMPHENOL INTERCONNECT PRODUCTS CORP. IS PROHIBITED.

AIPC P/N	DESCRIPTION	CUSTOMER P/N	POWER CONSUMPTION	ATTENUATION	EYE & JITTER TEST	EPROM REV
647080001	QSFP LOOPBACK W/MODSEL	SF-100GLB1.5W-0DB	1.5W	0 dB	NO	C
647080002	QSFP LOOPBACK W/MODSEL	SF-100GLB0W00-0DB	---	0 dB	NO	C
647080003	QSFP LOOPBACK W/MODSEL	SF-100GLB2.5W-0DB	2.5W	0 dB	NO	C
647080004	QSFP LOOPBACK W/MODSEL	SF-100GLB1.5W-3DB	1.5W	3 dB	YES	C
647080005	QSFP LOOPBACK W/MODSEL	SF-100GLB2.5W-3DB	2.5W	3 dB	YES	C
647080006	QSFP LOOPBACK W/MODSEL	SF-100GLB1.5W-5DB	1.5W	5 dB	YES	C
647080007	QSFP LOOPBACK W/MODSEL	SF-100GLB2.5W-5DB	2.5W	5 dB	YES	C
647080008	QSFP LOOPBACK W/MODSEL	SF-100GLB1.5W-6DB	1.5W	6 dB	YES	C
647080009	QSFP LOOPBACK W/MODSEL	SF-100GLB2.5W-6DB	2.5W	6 dB	YES	C
647080010	QSFP LOOPBACK W/MODSEL	SF-100GLB0W00-3DB	---	3 dB	YES	C
647080011	QSFP LOOPBACK W/MODSEL	SF-100GLB0W00-5DB	---	5 dB	YES	C
647080012	QSFP LOOPBACK W/MODSEL	SF-100GLB0W00-6DB	---	6 dB	YES	C
647080013	QSFP LOOPBACK W/MODSEL	SF-100GLB3.5W-0DB	3.5W	0 dB	NO	C
647080014	QSFP LOOPBACK W/MODSEL	SF-100GLB3.5W-3DB	3.5W	3 dB	YES	C
647080015	QSFP LOOPBACK W/MODSEL	SF-100GLB3.5W-5DB	3.5W	5 dB	YES	C
647080016	QSFP LOOPBACK W/MODSEL	SF-100GLB3.5W-6DB	3.5W	6 dB	YES	C

REVISIONS			
REV	DESCRIPTION	DATE	APPROVED
A	NEW RELEASE PER EO 306707	11/15	DEC
B	REVISED PER ECN 306741	11/15	DEC
C	REVISED PER ECN 306765	12/15	DEC



- THIS DRAWING IS RESERVED FOR AMPHENOL ACD (NO CUSTOMER DRAWING).
- PERMANENTLY MARK LABEL WITH INDICATED TEXT.
- ALL MATERIALS USED IN THE MANUFACTURE OF THIS ASSEMBLY SHALL COMPLY WITH AMPHENOL REGULATED MATERIALS SPECIFICATION CS-1152.
- TEST COMPLETED ASSEMBLIES PER AMPHENOL CS-1089. TEST ASSEMBLIES AT 10.31 Gbps AS NOTED IN P/N TABLE.
- SIMILAR TO AMPHENOL SPEC 63051XXXX.
- PROGRAM EPROM PER CS-1154. EPROM SERIAL No. MUST MATCH LABEL SERIAL No.
- INSTALL DUST COVER (ITEM 9) OVER CONNECTOR. COMPLETED ASSY SHALL BE PACKAGED IN AN APPROPRIATELY SIZED ANTI-STATIC BAG. PERMANENTLY LABEL BAG PER BAG LABEL DETAIL.



**SPECIFICATION CONTROL DRAWING**

UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN INCHES TOLERANCES ARE: DECIMALS .X ±.X .XX ±.01 .XXX ±.005 ANGLES ±.5°	EAR NO.		<b>Amphenol Interconnect Products Corp.</b> 20 Valley St. Endicott, NY, 13760
	APPROVALS	DATE	
THIRD ANGLE PROJECTION	DRAWN D. CASHIMERE	11/15	ASSEMBLY, LOOPBACK, QSFP, W/MODSEL & POWER OPTIONS, 25Gbps
	CHECKED		
	RESP ENG		SIZE DWG. NO. 64708XXXX
	MFG ENG		REV. C