





THE INFORMATION CONTAINED IN THIS DRAWING IS THE SOLE PROPERTY OF L-COM, INC. ANY REPRODUCTION IN PART OR WHOLE WITHOUT THE WRITTEN PERMISSION OF L-COM, INC. IS PROHIBITED.

| REVISIONS | | | |
|-----------|-----------------|------------|------------|
| REV | DESCRIPTION | DATE | APPROVED |
| A | INITIAL RELEASE | 10/13/2020 | MBLACKWOOD |
| | | | |
| | | | |





| PART NUMBER | L FEET | L METERS |
|---------------|--------|----------|
| PPA00017-3FT | 3 | 0.91 |
| PPA00017-6FT | 6 | 1.83 |
| PPA00017-8FT | 8 | 2.44 |
| PPA00017-10FT | 10 | 3.05 |



NOTES:

1. APPROVALS: UL, cUL.
2. RATING: 15A/250V.
3. COLOR CODING: BLACK, WHITE, GREEN.
4. CABLE ASSEMBLY SHALL BE INDIVIDUALLY PACKAGED IN ACCORDANCE WITH SPEC. PS-0031.

| | | | | | |
|--|----------------------------|---------------------------|--|---|------------------|
| UNLESS OTHERWISE SPECIFIED, DIMENSIONS ARE IN INCHES [mm] OVERALL CABLE LENGTH TOLERANCE: ≤12 [305] = +1 [25] / -0 >12 [305] ≤60 [1524] = +2 [51] / -0 >60 [1524] ≤120 [3048] = +4 [102] / -0 >120 [3048] ≤300 [7620] = +6 [152] / -0 >300 [7620] = +5% / -0 ALL OTHER DIMENSIONAL TOLERANCES: .X = ± .2 [5] FRACTIONS ± 1/32 .XX = ± .02 [.5] ANGLES ± 1° .XXX = ± .005 [.13] | APPROVALS | DATE |  50 High Street, West Mill, North Andover, MA 01845 USA. Phone: 1.800.341.5266 1.978.682.6936 | | |
| | DRAWN BY DZINN | 10/13/2020 | | | |
| THIRD-ANGLE PROJECTION  | CHECKED BY DFRISIELLO | 10/13/2020 | CATEGORY POWER PRODUCTS | | |
| | APPROVED BY MBLACKWOOD | 10/13/2020 | | PRODUCT DESCRIPTION Nema L6-20P to C13 Power Cord, 15A, 250V | |
| CONFIGURATION DETAILS OF UNDIMENSIONED FEATURES MAY VARY | COLOR VARIATIONS MAY OCCUR | SIZE A | CAGE CODE 43321 | ITEM NO. PPA00017 | REV. A |
| SCALE: NONE | | CAD FILE: PPA00017.SLDDRW | | SHEET 1 OF 1 | |