




Any unauthorized use of this drawing, copying or passing on to third parties requires the explicit approval of ebm-papst Mulfingen GmbH & Co. KG. Any violations of this shall be prosecuted in Civil and Penal Court!



技术说明:

1. 230V, 50/60Hz, 10/9W
2. 安装方式不变, 通过两只M4x16安装

Technical Instruction:

1. 230V, 50/60Hz, 10/9W
2. The installation mode remains unchanged, 2xM4x16

| | | | | | | | | | | |
|--------------|--|--|--|--|----------|---------|------|------|--------|------------|
| Tolerances | ebmpapst | | | | | | | | | |
| | ebm-papst Ventilator (ShangHai) CO., Ltd | | | | | | | | | |
| Scale | Production outline drawing | | | | | | | | Fit | Deviations |
| Size | M4Q045-CA25-F3 | | | | Date | Name | | | | |
| Distribution | | | | | Designed | Checked | CAD: | Ind. | KM-Nr. | Date |

Paper size: A3