

ITEM	PART#	DESCRIPTION	QTY	UOM
A, B	5601230800	DURACLIK ISL HOUSING 8P	2	PC
C	5601250800	DURACLIK ISL RETAINER 8P	2	PC
D	5601240101	DURACLIK ISL crimp receptacle terminal	16	PC
E	--	PAPER PRINTED PAPER WHITE	1	PC

FROM	TO	DESCRIPTION	COLOR
A1	B8	1X0.35 SQMM PVC BARE CU BK FLRY-A	BLACK
A2	B7	1X0.35 SQMM PVC BARE CU BK FLRY-A	BLACK
A3	B6	1X0.35 SQMM PVC BARE CU BK FLRY-A	BLACK
A4	B5	1X0.35 SQMM PVC BARE CU BK FLRY-A	BLACK
A5	B4	1X0.35 SQMM PVC BARE CU BK FLRY-A	BLACK
A6	B3	1X0.35 SQMM PVC BARE CU BK FLRY-A	BLACK
A7	B2	1X0.35 SQMM PVC BARE CU BK FLRY-A	BLACK
A8	B1	1X0.35 SQMM PVC BARE CU BK FLRY-A	BLACK




TABLE			
PART NUMBER	L1	L2 (REF)	TITLE
2183221081	150±8	63	DURA-CLIK ISL R-R 8CKT 150MM DISC Sn
2183221082	300±10	138	DURA-CLIK ISL R-R 8CKT 300MM DISC Sn
2183221083	600±10	288	DURA-CLIK ISL R-R 8CKT 600MM DISC Sn

- NOTES
1. Cable assembly must pass 100% for continuity and polarity.
 2. Connector view shown is from mating side.
 3. Label text must be 2mm max. in height with Arial font.
 4. Label must be wrapped in Flag type on a single cable.

MOLEX P/N
MOLEX
BATCH WK/YR
DETAIL A

REVISION			
DATE	REV	DESCRIPTION	CHANGER
24/05/2021	A	INITIAL RELEASE	ARAJU

FUNCTIONAL SYMBOLS $\frac{E}{A} = 0$ $\frac{E}{E} = 0$ $\frac{E}{P} = 0$ DIVISIONAL SYMBOLS	DIMENSION UNITS: mm SCALE: NTS GENERAL TOLERANCES (UNLESS SPECIFIED): ANGULAR TOL: ± ° 4 PLACES: ± 3 PLACES: ± 2 PLACES: ± 1 PLACE: ± 0 PLACES: ±	CURRENT REV DESC: EC NO: 665457 DRWN: ARAJU 2021/05/22 CHK'D: RDESAI01 2021/05/28 APPR: RDESAI01 2021/05/28 INITIAL REVISION: DRWN: ARAJU 2021/05/22 APPR: RDESAI01 2021/05/28				
	DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS					THIRD ANGLE PROJECTION
	PRODUCT CUSTOMER DRAWING		DOCUMENT NUMBER: 2183221081	DOC TYPE: PSD	DOC PART: 000	REVISION: A
	MATERIAL NUMBER: SEE TABLE		CUSTOMER: GENERAL MARKET		SHEET NUMBER: 1 OF 1	