




GENERAL TOLERANCES (UNLESS SPECIFIED)	
10 ^{UNDER}	±0.2
10 ^{OVER} 30 ^{UNDER}	±0.25
30 ^{OVER}	±0.3
ANGULAR	±3 °

DIMENSION UNITS	SCALE
mm	NTS
GENERAL TOLERANCES (UNLESS SPECIFIED)	
ANGULAR TOL	± °
4 PLACES	±
3 PLACES	±
2 PLACES	±
1 PLACE	±
0 PLACES	±
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

CURRENT REV DESC:			
EC NO: 719890	2022/08/22	molex	
DRWN: NARENC	2022/09/05		
CHK'D: SMARUYAMA	2022/09/05		
APPR: YNAITO	2022/09/05	PRODUCT CUSTOMER DRAWING	
INITIAL REVISION:		DOCUMENT NUMBER	DOC TYPE
DRWN: YSAKIYAMA	2004/01/27	SD-54104-072	PSD
APPR: MSASAO	2004/01/29		
THIRD ANGLE PROJECTION	DRAWING	SERIES	MATERIAL NUMBER
	A3-SIZE	54104	SEE TABLE


DOC PART	REVISION	SHEET NUMBER	
001	B	1 OF 2	

44	49.4	45.4	30.8	31.9	26.1	29.6	54104-5096	50	
			28.8	29.9	24.1	27.6	4	-4696	46
			28.3	29.4	23.6	27.1		-4596	45
			25.8	26.9	21.1	24.6		-4096	40
			24.8	25.9	20.1	23.6		-3896	38
			23.8	24.9	19.1	22.6		-3696	36
			23.3	24.4	18.6	22.1		-3596	35
			22.8	23.9	18.1	21.6		-3496	34
			22.3	23.4	17.6	21.1		-3396	33
			21.8	22.9	17.1	20.6	7	-3296	32
			20.8	21.9	16.1	19.6	54104-3096	30	
キャリアテープ幅 CARRIER TAPE WIDTH	F	E	D	C	B	A	MATERIAL NO.	CIRCUIT	

MODEL NO. 54104-**96

NOTES

1. 梱包数量：1500個／リール
NUMBER OF CONNECTORS：1500PCS／REEL
2. リードテープ長さ LEAD TAPE LENGTH




3. トップテープの剥離強度：0.1～1.3N {10～130gf}
(剥離方向は下図参照)


尚、本規格値は出荷時に適用。(但し、輸送時に剥離が発生しないこと。)

PEELING OFF FORCE OF TOP TAPE：0.1～1.3N {10～130gf}
(PEELING DIRECTION AS SHOWN IN FOLLOWING FIG.)

THIS REQUIREMENT SHOULD BE APPLIED AT SHIPMENT.
PEEL OFF SHOULD NOT BE ALLOWED, DURING TRANSPORTATION.






引き出し方向
PULL OUT
DIRECTION



DETAIL "G"

4. 材料(MATERIAL)
キャリアテープ(CARRIER TAPE)：ポリプロピレン(POLYPROPYLENE)
トップテープ(TOPTAPE)：PET , PE , PEF
リール(REEL)：ポリスチレン(PS)<リサイクル材を含む>
POLYSTYRENE (PS)<RECYCLE MATERIAL CONTAINED>

5. 本製品は 54104-**92 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 54104-**92.



GENERAL TOLERANCES (UNLESS SPECIFIED)	
10 ^{UNDER}	±0.2
10 ^{OVER} 30 ^{UNDER}	±0.25
30 ^{OVER}	±0.3
ANGULAR	±3 °

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION													
DIMENSION UNITS		SCALE		CURRENT REV DESC:		molex EMBSTP PKG FOR 0.5 FPC CONN. ZIF HSG ASSY -LEAD FREE- PRODUCT CUSTOMER DRAWING							
mm		NTS											
GENERAL TOLERANCES (UNLESS SPECIFIED) ANGULAR TOL ± ° 4 PLACES ± 3 PLACES ± 2 PLACES ± 1 PLACE ± 0 PLACES ±		EC NO: 719890		2022/08/22						DOCUMENT NUMBER		DOC TYPE	
		DRWN: NARENC		2022/09/05									
		CHK'D: SMARUYAMA		2022/09/05									
		APPR: YNAITO		2004/01/27		SD-54104-072		PSD		001		B	
		INITIAL REVISION:		2004/01/29									
		DRWN: YSAKIYAMA		2004/01/27		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER			
APPR: MSASAO		2004/01/29											
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS		THIRD ANGLE PROJECTION		DRAWING		SERIES		SEE SHEET 1		GENERAL MARKET		2 OF 2	
				A3-SIZE		54104							

DOCUMENT STATUS	P1	RELEASE DATE	2022/09/05	05:51:57
-----------------	----	--------------	------------	----------