


BACKSHELL KIT INCLUDES:

- (1) BACKSHELL
- (2) 4-40 THUMBSCREWS
- (1) PLASTIC STRAIN RELIEF
- (1) METAL STRAIN RELIEF CLAMP
- (2) STRAIN RELIEF SCREW



TOLERANCES ±0.020 (±0.50)
UNLESS OTHERWISE NOTED

SPECIFICATIONS:

MATERIALS

BACKSHELL: PA66, UL 94 HB
THUMBSCREWS: STEEL, BLACK OXIDE (FOR BLACK COLOR)
STEEL, ZINC PLATED (FOR ALL OTHER COLORS)

ENVIRONMENT

OPERATING TEMPERATURE: -55°C TO +110°C

RECOMMENDED TORQUE VALUE

FOR STRAIN RELIEF SCREWS: 4 IN-LB MAX

COLOR	COLOR RANGE	
	UPPER BOUND	LOWER BOUND
01 = BLACK	PANTONE BLACK 3C	PANTONE BLACK 3C
03 = LIGHT GREY	427C	427C
04 = GREEN	7731C	7732C
06 = RED	186C	187C
07 = BLUE	2190C	2191C
08 = YELLOW	108C	109C
11 = DEC GREY	7527C	7534C
0W = WHITE	N/A	N/A

972-009-01SRYY1

SERIES
POSITIONS
009
MATERIAL
01S = PLASTIC/SLIM LINE
COLOR
01 = BLACK
03 = LIGHT GREY
04 = GREEN
06 = RED
07 = BLUE
08 = YELLOW
11 = DEC GREY
0W = WHITE
PACKAGING
1 = KIT

RoHS COMPLIANT



THESE DRAWINGS AND SPECIFICATIONS ARE THE PROPERTY OF NorComp AND SHALL NOT BE REPRODUCED, COPIED OR USED AS THE BASIS FOR THE MANUFACTURE OR SALE OF APPARATUS WITHOUT WRITTEN PERMISSION.

DRAWN:
M. SIGMON

DATE:
07/06/2015

UNITS = inches (mm)

DO NOT SCALE FROM DRAWING

NorComp

SCALE: NTS	SHEET 1	OF 1	REV 1
DWG NO. 972-009-01SRYY1			