


SNAP-IN CABLE HANGER

1/2" COAX CABLE




MOLEX P/N	DESCRIPTION
0734300110	SNAP-IN HANGER FOR 1/2" COAX CABLE

7/8" COAX CABLE



MOLEX P/N	DESCRIPTION
0734300111	SNAP-IN HANGER FOR 7/8" COAX CABLE

1 1/4" COAX CABLE



MOLEX P/N	DESCRIPTION
0734300112	SNAP-IN HANGER FOR 1 1/4" COAX CABLE

1 5/8" COAX CABLE



MOLEX P/N	DESCRIPTION
0734300113	SNAP-IN HANGER FOR 1 5/8" COAX CABLE

2 1/4" COAX CABLE



MOLEX P/N	DESCRIPTION
0734300114	SNAP-IN HANGER FOR 2 1/4" COAX CABLE

MATERIAL:
21 GAUGE STAINLESS STEEL 304

PROPERTIES:
CORROSION RESISTANT
OPERATING TEMPERATURE: -40° / +85° C
RoHS COMPLIANT

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
FUNCTIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC: NEW DRAWING RELEASE					molex SNAP-IN HANGER VARIOUS SIZE COAXIAL CABLES		
= 0 = 0 = 0	- NTS		GENERAL TOLERANCES (UNLESS SPECIFIED)									
		MM	INCH									
DIVISIONAL SYMBOLS		4 PLACES	±	±								
		3 PLACES	±	±								
		2 PLACES	±	±								
		1 PLACE	±	±								
		0 PLACES	±	±								
		ANGULAR TOL	±	0.5°								
		DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS										