




COLD SHRINK TUBE:




MOLEX P/N	DESCRIPTION
0734300190	COLD SHRINK TUBE, SILICONE, 1 3/4" I.D. X 5.0" LONG



MOLEX P/N	DESCRIPTION
0734300191	COLD SHRINK TUBE, SILICONE, 1 9/16" I.D. X 5.0" LONG



MOLEX P/N	DESCRIPTION
0734300192	COLD SHRINK TUBE, SILICONE, 1.0" I.D. X 4.0" LONG



MOLEX P/N	DESCRIPTION
0734300193	COLD SHRINK TUBE, SILICONE, 9/16" I.D. X 3.0" LONG

MATERIAL:
SILICONE

PROPERTIES:
UV RESISTANT
OPERATING TEMPERATURE: -40° / +85° C
IP67 RATED
RoHS COMPLIANT

FUNCTIONAL SYMBOLS	THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
= 0 = 0 = 0	DIMENSION UNITS		SCALE		CURRENT REV DESC: NEW DRAWING RELEASE				molex SILICONE COLD SHRINK VARIOUS SIZES						
	MM		NTS												
	GENERAL TOLERANCES (UNLESS SPECIFIED)								PHASE: CO NO: CO-000015067 DRWN: Les Meier 2024-06-06 CHK'D: James Borrelli 2024-09-09 APPR: Les Meier 2024-09-09						
DIVISIONAL SYMBOLS			MM	INCH					PRODUCT CUSTOMER DRAWING						
	4 PLACES	±		±					DOCUMENT NUMBER		DOC TYPE	DOC PART	REVISION		
	3 PLACES	±		±					734300190		PSD	000	A		
	2 PLACES	±		±											
	1 PLACE	±		±	INITIAL REVISION:										
	0 PLACES	±		±	DRWN: Les Meier 2024-06-06 APPR: Les Meier 2024-09-09										
ANGULAR TOL ± 0.5°															
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						C-SIZE		73430		SEE TABLES				1 OF 1	