




COLD SHRINK TUBE:




MOLEX P/N	DESCRIPTION
0734300190	COLD SHRINK TUBE, SILICONE, 1 3/4" I.D. X 5.0" LONG



MOLEX P/N	DESCRIPTION
0734300191	COLD SHRINK TUBE, SILICONE, 1 9/16" I.D. X 5.0" LONG



MOLEX P/N	DESCRIPTION
0734300192	COLD SHRINK TUBE, SILICONE, 1.0" I.D. X 4.0" LONG



MOLEX P/N	DESCRIPTION
0734300193	COLD SHRINK TUBE, SILICONE, 9/16" I.D. X 3.0" LONG

MATERIAL:
SILICONE

PROPERTIES:
UV RESISTANT
OPERATING TEMPERATURE: -40° / +85° C
IP67 RATED
RoHS COMPLIANT

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION														
FUNCTIONAL SYMBOLS	DIMENSION UNITS		SCALE		CURRENT REV DESC: NEW DRAWING RELEASE					molex SILICONE COLD SHRINK VARIOUS SIZES				
	MM	NTS												
	GENERAL TOLERANCES (UNLESS SPECIFIED)									PHASE: CO NO: CO-000015067 DRWN: Les Meier 2024-06-06 CHK'D: James Borrelli 2024-09-09 APPR: Les Meier 2024-09-09				
			MM	INCH										
DIVISIONAL SYMBOLS	F	= 0												
	E	= 0												
	P	= 0												
	PRODUCT CUSTOMER DRAWING													
													</	