




COMMENT:
ALL RIGHTS ARE RESERVED BY US FOR THIS DRAWING. WITHOUT OUR PRIOR CONSENT,
IT MAY NEITHER BE DUPLICATED NOR MADE AVAILABLE TO A THIRD PARTY.
AND IT ALSO MAY NOT BE IMPROPERLY USED BY THE RECEIVER, OR A THIRD PARTY.



1	2		3		4		5	6	7	8
Material-No.	Order-No.	Shell Size / for No. of Contacts	A	B	C	D	E	øF1		
1731110948	FKPP1	1 / 9	37.4	45.2	23°	2 x □12	15.2	3.3 - 7.5		
1731110949	FKPP2	2 / 15	45.7	45.2	2 x 23°	3 x □12	15.2	3.3 - 7.5		
1731110950	FKPP3	3 / 25	59.4	45.2	2 x 30°	3 x □12	15.2	3.3 - 7.5		




max. torque are 35 Ncm
Parts not mounted

FKPP1 with 1 blind plate (Part-No. 3)
FKPP2-3 with 2 blind plates (Part-No. 3)


Recommended assembly:




RoHS compliant



Size 1



Size 2



Size 3

5	2	Screw	Steel	
4	1	Cable clamp	Steel	
3	1/2	Blind plate	Plastic	black
2	1	Moveable cover	Plastic	black
1	1	Hood	FKPP Plastic	black
No.	St.	Part	Type Description/Material	Surface plating/Colour/Class

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION									
FUNCTIONAL SYMBOLS ▽ F = 0 ▽ E = 0 ▽ P = 0		DIMENSION UNITS mm		SCALE 2:1		MEASUREMENTS WITHOUT TOLERANCE ACC. TO ISO 2768-mK		molex FCT Plastic Hood	
						CURRENT REVISION			
						DRWN: DRAWN BY gkrimshandl 17-10-2025			
						APPR: APPR BY mateof 20-10-2025			
						INITIAL REVISION		PRODUCT CUSTOMER DRAWING	
						DRWN: DRAWN BY gkrimshandl 17-10-2025		MATERIAL NUMBER	
						APPR: APPR BY mateof 20-10-2025		see table	
		1						REVISION	
		REV.		CH.-NO.				1	
		REPLACEMENT FOR: FMK1-5_SW		FRIST ANGLE PROJECTION 		DRAWING A3-SIZE		DOCUMENT NUMBER FKPP1-3	
								CUSTOMER GENERAL MARKET	
								SHEET NUMBER 1 OF 1	