




THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2015. © COPYRIGHT 2010 BY TE CONNECTIVITY ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS					
		P	LTR	DESCRIPTION	DATE	DWN	APVD
			B	REVISED PER ECO-15-005416	22JUL2015	JA	DM
			B1	REVISED PER ECO-16-012884	31AUG2016	JA	DM
			C	REVISED PER PCN-24-219306	29AUG2024	CO	CB
			D	REVISED PER PCN-25-233228	19DEC2024	RK	CB

5. 3 SIZE 4: 4 AWG [21.0-25.0 mm²] AND 4 SIZE 16.

4 NOTED DIMENSION DOES NOT INCLUDE GROMMET PROTRUSION.


3 MATERIAL: PLUG HOUSING/COUPLING RING: PA66 GF10 (BLACK)
RETAINING RING: PA66 GF10 (GREEN)
GROMMET: SILICONE (ORANGE-RED)

2 SEE 0425-021-0000 APPLICATION SPECIFICATION
A. RECOMMENDED WIRE INSULATION RANGE
B. CONTACT REMOVAL TOOL

1. THIS PLUG MATES WITH HDP24-24-7PX-XXXX RECEPTACLE
X = SEAL TYPE (N,T,E)
XXXX = MODIFICATION

NOTES:

TE INTERNAL PN	DEUTSCH PN
HDP26-24-7SN-C038	HDP26-24-7SN-C038

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN	01APR2010	 TE Connectivity		
		CHK	05AUG2010			
		APVD	05AUG2010			
		PRODUCT SPEC	0425-021-0000			
DIMENSIONS: INCHES[mm]		TOLERANCES UNLESS OTHERWISE SPECIFIED:		NAME PLUG CONNECTOR SHELL SIZE 24, -C038 MOD HDP SERIES		
		0 PLC	±	SIZE A3		
		1 PLC	±			
		2 PLC	±	CAGE CODE 4AFU8		
		3 PLC	±.015 [0.38]			
		4 PLC	±	DRAWING NO HDP26-24-7SN-C038		
		ANGLES	±0°30'0"			
MATERIAL		FINISH		RESTRICTED TO -		
3						
Customer Drawing				SCALE	2:1	SHEET 1 OF 1
				REV D		