

NOTES:
ALL DIMENSIONS ARE NOMINAL FOR REFERENCE
ONLY UNLESS OTHERWISE STATED.

RoHS: COMPLIANT.

SPECIFICATIONS:
IMPEDANCE: 50Ω
FREQUENCY: DC TO 9GHz


VSWR	INSERTION LOSS	FEEQUENCY,GHz
<1.25	0.20	@DC 0.01≤ f ≤ 2GHz
<1.45	0.45	2< f ≤ 6 GHz
<1.55	0.50	6< f ≤ 7 GHz
<1.75	0.55	7< f ≤ 9 GHz

SHIELDING
FREQUENCY NEXT LIMIT
2 GHz<f<5GHz ≤-55dB
5 GHz<f<9GHz ≤-50dB

TEST VOLTAGE: 800 VRMS
WORKING VOLTAGE: ≤60V DC
CURRENT RATING: ≤1A DC

MECHANICAL CHARACTERISTICS
MATING CYCLES: ≥25.
ENGAGEMENT FORCE: ≤45 N.
DISENGAGEMENT FORCE: ≥2 N.
RETENTION FORCE LATCH: ≥110 N.

ENVIRONMENTAL PARAMETER
TEMPERATURE RANGE: -40°C TO +105°C.
WATER TIGHTNESS: IP67&IP6K9K.



CODING	COLOR
A	JET BLACK
B	CREAM WHITE
C	SIGNAL BLUE
D	CLARET VIOLET
E	LEAF GREEN
F	NUT BROWN
G	BLUE GREY
H	LIGHT PINK
J	BEIGE
K	CURRY
N	PASTEL GREEN
Z	WATER BLUE

CONFIGURATION TABLE




TEPN	DESCRIPTION	CODING
2545465-1	MINI-FAKRA JACK 2P STR A-CODE HSG WP	A
2545465-2	MINI-FAKRA JACK 2P STR B-CODE HSG WP	B
2545465-3	MINI-FAKRA JACK 2P STR C-CODE HSG WP	C
2545465-4	MINI-FAKRA JACK 2P STR D-CODE HSG WP	D
2545465-5	MINI-FAKRA JACK 2P STR E-CODE HSG WP	E
2545465-6	MINI-FAKRA JACK 2P STR F-CODE HSG WP	F
2545465-7	MINI-FAKRA JACK 2P STR G-CODE HSG WP	G
2545465-8	MINI-FAKRA JACK 2P STR H-CODE HSG WP	H
2545465-9	MINI-FAKRA JACK 2P STR J-CODE HSG WP	J
1-2545465-0	MINI-FAKRA JACK 2P STR K-CODE HSG WP	K
1-2545465-1	MINI-FAKRA JACK 2P STR N-CODE HSG WP	N
1-2545465-2	MINI-FAKRA JACK 2P STR Z-CODE HSG WP	Z

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ± - 1 PLC ± 0.3 2 PLC ± 0.2 3 PLC ± 0.1 4 PLC ± - ANGLES ± 5 FINISH -
MATERIAL SEE TABLE	

DWN TP	24JUN2026	TE Connectivity Ltd.			
CHK TP	24JUN2026				
APVD ARAVIND	24JUN2026	NAME MINI-FAKRA JACK 2P STR X-CODE HSG WP			
PRODUCT SPEC					
APPLICATION SPEC					
WEIGHT SEE NOTE		SIZE A3	CAGE CODE 00779	DRAWING NO C=2545465	RESTRICTED TO -
CUSTOMER DRAWING		SCALE 1:1	SHEET 1 OF 4	REV A	

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	GTP;ECN-26-395384	23JUL2026	TP	AV



NOTES:
FINISH (PLATING THICKNESS IN MICRO-INCHES)

- 100 MICROINCHES MIN MATTE TIN PLATED.
(10WT%P) MICROINCHES MIN OVER NICKEL UNDERPLATED.
50 MICROINCHES MIN OVER COPPER UNDERPLATED.
- 50 MICROINCHES MIN NICKEL PLATED.
- 5 MICROINCHES MIN GOLD PLATED.
(10WT%P) MICROINCHES MIN OVER NICKEL UNDERPLATED.
50 MICROINCHES MIN OVER COPPER UNDERPLATED.

NOTE 3	PHOSPHOR BRONZE	TERMINAL	6
NOTE 2	STAINLESS STEEL	CRIMP	5
YELLOW GREEN	PBT 30%GF	BACK COVER	4
REFER COMPONENTS TABLE	SILICONE RUBBER	SEALING RING 1	3
NOTE 1	PHOSPHOR BRONZE	OUTER CONTACT	2
UL94 V0 (REF CODING COLOR)	PA66 30%GF	HOUSING	1
FINISH/PLATING/GRADE	MATERIAL	DESCRIPTION	ITEM

PARTS LIST

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—


NOTES:
THE FINISH GOODS REQUIRE SEPARATION OF INDIVIDUAL COMPONENTS FOR ASSEMBLY.

EACH FINISH GOOD COMPONENTS REFER TO PART NUMBER (TCPN) TABLE AS SHOW ON THE DRAWING SHEET 2 & 3.

QTY PER PACKAGING AS SHOW ON THE TABLE, DRAWING SHEET 2 & 3. DETAIL COMPONENTS & PACKAGING SPEC, REFER COMPONENT DRAWING.

ASSEMBLY INSTRUCTION REFER TO TE.COM FOR EACH FINISH GOOD PART NUMBERS

PRODUCT WEIGHT: 3.36 g



COMPONENTS TABLE: X-2545465-X FOR CABLE RTK031

TEPN	DESCRIPTION	QPA	PACKAGING SPEC & QTY
X-2545465-X	HOUSING (REFER TO 1ST PAGE CONF-TABLE)	1	500 PCS./BAG , 4000 PCS./BOX.
2554540-1	CONTACT SUB-ASSEMBY	2	1000 PCS./REEL , 8000 PCS./BOX.
2554545-1	TERMINAL	2	4000 PCS./REEL , 24000 PCS./BOX.
2554584-1	CRIMP	2	1500 PCS./REEL , 12000 PCS./BOX.
2554559-1	SEALING RING FOR 2P RTK301 (WHITE)	1	2000 PCS./BAG , 4 BAG./BOX.
2554561-1	BACK COVER 2P (YELLOW)	1	2000 PCS./BAG , 4 BAG./BOX.

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TP	24JUN2026	TE Connectivity Ltd.		
		CHK TP	06APR2026			
DIMENSIONS: mm		APVD ARAVIND	06APR2026	NAME MINI-FAKRA JACK 2P STR X-CODE HSG WP		
		PRODUCT SPEC	—	—		
		APPLICATION SPEC	—	—		
MATERIAL SEE TABLE		WEIGHT	3.36 g	SIZE A3	CAGE CODE 00779	DRAWING NO C=2545465
		FINISH	—	RESTRICTED TO —		
CUSTOMER DRAWING				SCALE 1:1	SHEET 2 of 4	REV A

NOTES:
THE FINISH GOODS REQUIRE SEPARATION OF INDIVIDUAL COMPONENTS FOR ASSEMBLY.


EACH FINISH GOOD COMPONENTS REFER TO PART NUMBER (TCPN) TABLE AS SHOW ON THE DRAWING SHEET 2 & 3.

QTY PER PACKAGING AS SHOW ON THE TABLE, DRAWING SHEET 2 & 3. DETAIL COMPONENTS & PACKAGING SPEC, REFER COMPONENT DRAWING.

ASSEMBLY INSTRUCTION REFER TO TE.COM FOR EACH FINISH GOOD PART NUMBERS


PRODUCT WEIGHT: 3.44 g

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—




COMPONENTS TABLE: X-2545465-X FOR CABLE RG174

TEPN	DESCRIPTION	QPA	PACKAGING SPEC & QTY
X-2545465-X	HOUSING (REFER TO 1ST PAGE CONF-TABLE)	1	500 PCS./BAG , 4000 PCS./BOX.
2554542-1	CONTACT SUB-ASSEMBY	2	1000 PCS./REEL , 8000 PCS./BOX.
2554545-1	TERMINAL	2	4000 PCS./REEL , 24000 PCS./BOX.
2554549-1	CRIMP	2	1500 PCS./REEL , 12000 PCS./BOX.
2554560-1	SEALING RING FOR 2P RG174 (RED)	1	2000 PCS./BAG , 4 BAG./BOX.
2554561-1	BACK COVER 2P (YELLOW)	1	2000 PCS./BAG , 4 BAG./BOX.



THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TP	24JUN2026	 TE Connectivity Ltd.		
		CHK TP	07APR2026			
DIMENSIONS: mm		APVD ARAVIND	07APR2026	NAME MINI-FAKRA JACK 2P STR X-CODE HSG WP		
		PRODUCT SPEC				
		APPLICATION SPEC				
MATERIAL SEE TABLE		WEIGHT	3.44 g	SIZE A3	CAGE CODE 00779	DRAWING NO C=2545465
		CUSTOMER DRAWING		SCALE	1:1	SHEET 3 OF 4
				REV A		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	—	SEE SHEET 1	—	—	—

SEAL THE BOX WITH
ADHESIVE TAPE




QTY, REFER TO
COMPONENTS TABLE
PACKAGING SPEC & QTY




REEL/BOX PACKAGING METHOD.

PAD X 2






CORNER GUARD X 4




CARTON * 1
SIZE: L X W X H MM

SEAL THE BOX WITH
ADHESIVE TAPE




QTY, REFER TO
COMPONENTS TABLE
PACKAGING SPEC & QTY

BAG/BOX PACKAGING METHOD.



REFER TO TCPN

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN TP	24JUN2026	 TE Connectivity Ltd.		
		CHK TP	07APR2026			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD ARAVIND	NAME MINI-FAKRA JACK 2P STR X-CODE HSG WP	
		0 PLC ± —		PRODUCT SPEC	—	
		1 PLC ± 0.3		—	—	
		2 PLC ± 0.2		APPLICATION SPEC	—	
		3 PLC ± 0.1		—	—	
		4 PLC ± —		—	—	
MATERIAL SEE TABLE		FINISH —		WEIGHT —	SIZE A3	CAGE CODE 00779
				CUSTOMER DRAWING	DRAWING NO C=2545465	RESTRICTED TO —
					SCALE 1:1	SHEET 4 OF 4
						REV A