





注記 NOTES


1. 梱包数量：1000個/リール NUMBER OF CONNECTORS：1000PCS/REEL
2. リードテープ長さ LEAD TAPE LENGTH








3. トップテープの剥離強度についてはIEC60286-3に準拠。
TOP TAPE PEEL FORCE IS DEFINED BY IEC60286-3.
4. 材料 キャリアテープ：ポリプロピレン (PP)
トップテープ：PET, PE, PEF
リール：ポリスチレン (PS) <リサイクル材を含む>
- MATERIAL
CARRIER TAPE：POLYPROPYLENE
TOP TAPE：PET, PE, PEF
REEL：POLYSTYRENE (PS) <CONTAINED RECYCLE MATERIAL >
5. 本製品は53309-**91の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 53309-**91.

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION												
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex				
mm		NTS										
GENERAL TOLERANCES (UNLESS SPECIFIED)				EC NO: 653700 DRWN: AHMADI2 2021/02/03 CHK'D: HSHIMOYAMA 2021/02/26 APPR: SHOSHIKAWA 2021/02/26 INITIAL REVISION: DRWN: YSATO06 2017/03/23 APPR: TKUSUHARA01 2017/03/27								
ANGULAR TOL ± °												
4 PLACES ±												
3 PLACES ±												
2 PLACES ±												
1 PLACE ±												
0 PLACES ±												
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				PRODUCT CUSTOMER DRAWING								
				DOCUMENT NUMBER				DOC TYPE		DOC PART	REVISION	
				533090000				PSD		000	B	
THIRD ANGLE PROJECTION				DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER
				A2-SIZE		53309		SEE CHART				1 OF 3

DOCUMENT STATUS	P1	RELEASE DATE	2021/02/26	10:23:41
-----------------	----	--------------	------------	----------






0.4	17.8	16.9	15.2	53309-4070	40
0.4	16.2	15.3	13.6	53309-3670	36
0.4	14.6	13.7	12.0	53309-3270	32
0.8	13.8	12.9	11.2	53309-3070	30
0.4	13.0	12.1	10.4	53309-2870	28
0.8	12.2	11.3	9.6	53309-2670	26
0.4	11.4	10.5	8.8	53309-2470	24
0.8	10.6	9.7	8.0	53309-2270	22
0.4	9.8	8.9	7.2	53309-2070	20
0.8	9.0	8.1	6.4	53309-1870	18
0.4	8.2	7.3	5.6	53309-1670	16
0.8	7.4	6.5	4.8	53309-1470	14
0.4	6.6	5.7	4.0	53309-1270	12
0.8	5.8	4.9	3.2	53309-1070	10
D	C	B	A	EMBOSSSED TAPE PACKAGE	極數 CIRCUIT
				ORDER NO	

GENERAL TOLERANCES (UNLESS SPECIFIED)	
10 ^{UNDER}	±0.2
10 ^{OVER} 30 ^{UNDER}	±0.25
30 ^{OVER}	±0.3
ANGULAR±3°	
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS	

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT PERMISSION															
DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex							
mm		10:1													
GENERAL TOLERANCES (UNLESS SPECIFIED)				0.8 MM PITCH B-TO-B CONN. PLUG (WITHOUT BOSS)											
ANGULAR TOL		± °		EC NO: 750938				PRODUCT CUSTOMER DRAWING							
4 PLACES		±		DRWN: RAJAGN 2023/05/19											
3 PLACES		±		CHK'D: HSHIMOYAMA 2023/05/25											
2 PLACES		±		APPR: YNAITO 2023/05/25											
INITIAL REVISION:				DOCUMENT NUMBER				DOC TYPE		DOC PART		REVISION			
1 PLACE		±		DRWN: YSATO06 2017/03/23				533091000		PSD		000		C	
0 PLACES		±		APPR: TKUSUHARA01 2017/03/27											
DRAWING WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER	
						A2-SIZE		53309		SEE CHART				1 OF 2	



NOTES :

1. 嵌合相手：52465シリーズ
MATE WITH：52465 SERIES.
- △ 2. ウェハーの ㊦ から隣接するピンの ㊦ 迄の位置を示す。
SHOW POSSITION FROM ㊦ OF WAFER TO ㊦ OF ADJACENT PINS.
3. 本製品は53309-**27 の鉛フリー品である。
THIS PRODUCT IS LEAD FREE OF 53309-**27.
4. 使用材料MATERIAL
ハウジングHOUSING：PPS GLASS FILLED, UL94V-0 (WHITE)
ターミナルTERMINAL：燐青銅 PHOSPHOR BRONZE t=0.32
5. めっき仕様 PLATING
ターミナルTERMINAL：錫めっき/ニッケル下地 TIN OVER NICKEL PLATED
6. テール平坦度は0.1mm MAX
TAIL COPLANALITY TO BE 0.1mm MAXIMUM.

嵌合相手 MATE WITH
 52465-**70 (BOSSあり WITH BOSS)
 52465-**71 (BOSS無し WITHOUT BOSS)

嵌合状態図(参考)
MATED DRAWING (REF.)

THIS DRAWING CONTAINS INFORMATION THAT IS PROPRIETARY TO MOLEX ELECTRONIC TECHNOLOGIES, LLC AND SHOULD NOT BE USED WITHOUT WRITTEN PERMISSION																																	
GENERAL TOLERANCES (UNLESS SPECIFIED)		DIMENSION UNITS		SCALE		CURRENT REV DESC:				molex																							
		mm		20:1																													
GENERAL TOLERANCES (UNLESS SPECIFIED)		GENERAL TOLERANCES (UNLESS SPECIFIED)				ANGULAR TOL ± °										0.8 MM PITCH B-TO-B CONN. PLUG (WITHOUT BOSS)																	
																						PRODUCT CUSTOMER DRAWING											
										DOCUMENT NUMBER																		DOC TYPE		DOC PART		REVISION	
																												533091000					
										10° UNDER		±0.2		3 PLACES		±		EC NO: 750938		2023/05/19													
10° OVER 30° UNDER		±0.25		2 PLACES		±		DRWN: RAJAGN		2023/05/25																							
30° OVER		±0.3		1 PLACE		±		CHK'D: HSHIMOYAMA		2023/05/25																							
ANGULAR ±3°				0 PLACES		±		APPR: YNAITO																									
DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				DRAFT WHERE APPLICABLE MUST REMAIN WITHIN DIMENSIONS				THIRD ANGLE PROJECTION		DRAWING		SERIES		MATERIAL NUMBER		CUSTOMER		SHEET NUMBER															
										A2-SIZE		53309		SEE CHART				2 OF 2															