

PROXXON

PROXXON
MICROMOT
System

**Small, handy and powerful.
Easily drills steel up to a thickness of
5.0mm.**



Pocket drilling machine COLT 2



The pocket drilling

machine COLT 2 is supplied in a high-grade polypropylene storage case. It is attractive, extremely stable and sufficiently large to enable the machine to be replaced in it after completion of the work without fiddly refitting. A clear label on the side identifies the contents.

Tough and durable special, balanced, powerful, quiet and long-lasting DC motor. Quiet planetary gear gearbox of die-cast aluminium (main housing made of glass-fibre reinforced POLYAMIDE). Handy switch with integrated speed control and lock. The RÖHM chuck allows the precision removal of the inserts.

Technical data:

220 - 240V. 100W. 0 - 3,000rpm. RÖHM chuck capacity 0.5 - 6.0mm. Drilling capacity in steel 5.0mm. Length 225mm. Weight approx. 900g. Insulated to class 2.

NO 28 490