


**EVERBUILD ALL PURPOSE READY MIXED FILLER**

Colour	Product Code	Pack Size	Box Qty
White	RMFILL06	600G	12
	RMFILL1	1KG	12

**Product Description**

EVERBUILD ALL PURPOSE READY MIXED FILLER is an easy to use, ready mixed filler suitable for both interior and exterior use. When applied as directed, the filler dries to a smooth but tough crack resistant sandable finish, which may be painted, papered or stained.

**Benefits**

- Heavy-duty tough filler – interior or exterior use.
- Ready mixed formula – apply straight from tub.
- Overpaintable with most solvent based and emulsion paints.
- Overstainable
- Dries white.

**Areas For Use**

Fills gaps and holes in:

- Plaster
- Brick
- Stone
- Wood
- Render

**Limitations**

- Do not use to fill plastic or metals.
- Do not apply externally when rain is imminent (within 5 hours of application)
- Do not apply in temperatures (ambient and surface) below 5°C.
- Not suitable for repairs to permanently wet areas.
- Do not apply in layers more than 9mm deep. If deeper holes need filling, build up in layers allowing each layer to dry (about 1 hour) before applying further layer, or use ONE STRIKE LIGHTWEIGHT FILLER which may be applied in one application to a 75mm maximum depth.
- As the manufacturer cannot know all the uses its products may be put to, it is the users responsibility to determine suitability for use. If in doubt, contact technical Services Dept for advice.

### Surface Preparation

All surfaces must be clean, dry, free from dust, grease and other contamination. Provide a key to gloss painted surfaces. Cover nail or screw heads with oil based paint and allow to dry.

### Application

Stir well and apply directly from the tub with spatula/spreader. Press the filler into the repair to a maximum depth of 9mm. For deeper cavities, apply in layers and allow each to dry (1hour) Fill hole proud to allow for sanding and finish with a wet knife. Once dry, sand to a smooth finish. When used outdoors, seal repair with an oil based paint when fully dry.

Clean tools immediately after use with warm water.

### Specific Data

Appearance	White / Off White Powder
S.G. at 20°C	2.0gcm <sup>3</sup> (approx)
Movement Accommodation	Low – Dries hard
Maximum Fill	9mm in one coat -further layers may be built up
Maximum Width	25mm
Application Temperature	5°C to 30°C.
Drying Time	1-8 hours depending on depth and temperature
pH	8.5-9.5
Solids Content	85 -90% w/w

### Health & Safety

Consult MSDS for full list of hazards.

### Storage

Store at moderate temperatures. PROTECT FROM FROST

### Shelf Life

12 months when stored according to manufacturers instructions.

*The technical data contained herein is based on our present knowledge and experience and we cannot be held liable for any errors, inaccuracies, omissions or editorial failings that result from technological changes or research between the date of issue of this document and the date the product is acquired. Before using the product, the user should carry out any necessary tests in order to ensure that the product is suitable for the intended application. Moreover, all users should contact the seller or the manufacturer of the product for additional technical information concerning its use if they think that the information in their possession needs to be clarified in any way, whether for normal use or a specific application of our product. Our guarantee applies within the context of the statutory regulations and provisions in force, current professional standards and in accordance with the stipulations set out in our general sales conditions. The information detailed in the present technical data sheet is given by way of indication and is not exhaustive. The same applies to any information provided verbally by telephone to any prospective or existing customer.*