

Anna-50-7 series




Ordering number	C11670		
Description	C11670_Anna-50-7-S-OSL		
Family	Anna-50-7	FWHM	0 degrees
Type	Lens	Efficiency	-
LED	Oslon SSL 80	cd/lm	-
Color	Transparent	Gerber File	Available
Diameter	50 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		



Ordering number	C11679		
Description	C11679_Anna-50-7-M-OSL		
Family	Anna-50-7	FWHM	0 degrees
Type	Lens	Efficiency	-
LED	Oslon SSL 80	cd/lm	-
Color	Transparent	Gerber File	Available
Diameter	50 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		



Ordering number	C11682		
Description	C11682_Anna-50-7-W-OSL		
Family	Anna-50-7	FWHM	0 degrees
Type	Lens	Efficiency	-
LED	Oslon SSL 80	cd/lm	-
Color	Transparent	Gerber File	Available
Diameter	50 mm		
Height	10.7 mm		
Style	Round		
Optic Material	PMMA		
Holder Material	-		
Fastening	-		
Status	Ready		



Material: PMMA

- Versions:
 Anna-3-S
 Anna-3-M
 Anna-3-W
 Anna-4-S
 Anna-4-M
 Anna-4-W
 Anna-5-S
 Anna-5-M
 Anna-5-W
 Anna-6-S
 Anna-6-M
 Anna-6-W
 Anna-7-S
 Anna-7-M
 Anna-7-W

Number of cones varies;
 3, 4, 5, 6 and 7 pcs
 on bottom side depending
 the version.

This drawing is our property.
 It can't be reproduced
 or communicated without
 our written agreement.



DRAWING TITLE

DRAWN BY p		DATE 05.10.2010		Datasheet Anna50-series Lens			
CHECKED BY t k		DATE 03.08.2010					
DESIGNED BY hh		DATE 30.07.2010		SCALE 1:1	WEIGHT (g)	SHEET 1/1	

4

3

2

1

4

3

2

1

D

A