


Item no.: 250-212  
 Product description: 1-CONDUCTOR PCB TERMINAL STRIP 1 SOLDER PIN /  
 POLE STAGGERED 12 POLE PIN SPACING 3.5 MM / 0.138  
 IN WITH PUSH BUTTONS WITH TEST SLOT FOR TEST  
 PLUG TO 1.3 MM Ø



Produkt kann von Bild abweichen / product may differ

Packing unit 100 4\*25 pieces

Product group	4 (Printed Circuit)
Weight	5.73 g
Color	gray
No. of connection Points	12
No. of potentials	12
pole count	12
Height	13.1 mm
Height	0.516 in
Width	43.5 mm
Width	1.713 in
Depth	12 mm
Depth	0.472 in
Pin spacing from	3.5 mm
Pin spacing from	0.138 in
Pollution degree	2
Measured voltage EN	320 V
Measured shock voltage	2.5 kV
Current intensity EN	8 A

Pollution degree	2
Measured voltage EN	630 V
Measured shock voltage	2.5 kV
Current intensity EN	8 A



Cross section [mm <sup>2</sup> ]	0.2 - 1.5 mm <sup>2</sup>
Wiring method	solid
Cross section [mm <sup>2</sup> ]	0.2 - 1.5 mm <sup>2</sup>
Cross section [mm <sup>2</sup> ]	0.25 - 1 mm <sup>2</sup>
Cross section [mm <sup>2</sup> ]	0.25 - 1 mm <sup>2</sup>
Cross section [AWG]	24 - 16 AWG
Strip length from	8.5 mm
Strip length to	9.5 mm
Material group	I
xxx-xxx/000-002	yellow
xxx-xxx/000-004	black
xxx-xxx/000-005	red
xxx-xxx/000-006	blue
xxx-xxx/000-009	light gray
xxx-xxx/000-012	orange
xxx-xxx/000-014	brown
xxx-xxx/000-017	light green
xxx-xxx/000-024	violet
xxx-xxx/000-050	white



Item no.	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [ mm <sup>2</sup> ]
250-212	ABS	04-HG469925/1-PDA	400	2	0,5-1,5
250-212	BV	11915/A0	200	2	0,5-1,5
250-212	CCA	NL6336	400	8	0,2-1,5
250-212	CSA	154112-1132097	300	10	20-16
250-212	DNV	E-9215	400	2	0,5-1,5
250-212	GL	17296-00HH	400	2	0,5-1,5
250-212	KEMA	2114919.01	400	8	0,2-1,5
250-212	RMR	11130002	400	2	0,5-1,5
250-212	UR	E45171	600	2	20-16
250-212	UR	E45172	300/300	5/5	24-16

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected