

DELUXE APPRENTICE SET



Order Code: 188-8951

First ever toolkit bundle that includes technicians tool case!

Kit Includes:

- TECHNICIAN TOOL CASE PLUS: Size: 440x200x370mm; Material: 600 Denier Woven Polyester; Weight: 2.95kg
- MULTIMETER, DIGITAL, POCKET: DMM Handheld; Voltage Measuring Range: 300Vdc/Vac; Resistance Measuring Range:20M; Frequency Measuring Range:2kHz/20kHz; Capacitance Measuring Range:20
- SCREWDRIVER SET, INSULATED, 6PC: VDE Insulated Slotted and Crosshead PH Screwdrivers
- SCREWDRIVER SET, PRECISION, 6PC: Kit Contents:PH00, PH0, Slot 1.5, 2, 2.5, 3mm all 50mm long
- MINI PLIER SET, 5PC Kit Contents: Round Nose, Top Cutter, Flat Nose, Bent Nose, Diagonal Cutter; Handle Type: Two Tone Anti Slip
- CRIMP TOOL / WIRE STRIPPER Crimp Application: 1.5mm² - 6mm² Insulated Terminals
- HACKSAW, JUNIOR: Blade Length: 150mm; Tool Body Material: Steel; Length: 255mm
- TAPE MEASURE, 8M: Blade Width: 25mm; Case Color: Green; Tool Body Material: Plastic
- KNIFE, RETRACTABLE UTILITY: Blade Length: 25mm; Blade Width: 1mm; Material: Cast metal
- WRENCH, ADJUSTABLE, 6": Length: 150mm; Jaw Opening Max: 20mm
- TORCH, HARDCASE, 2AA: Battery Voltage: 1.5V; Yellow / Black; Length: 170mm; Light Source: LED
- HAMMER, BALL PEIN, 8OZ: Weight: 227g; Handle Type: Graphite / Resin; Head Type: Ball Pein
- MULTI PURPOSE SCISSOR 220MM: Scissor Type: Safety; Tool Body Material: Stainless Steel
- HEXAGON KEY SET, METRIC, BALL END, 9PC: 1.5, 2, 2.5, 3, 4, 5, 6, 8, 10mm Hex Keys; Hex Key Type: Ball End; Tool Body Material: Chrome Vanadium Steel