

List Price \$75.00 USD

Availability **Non-Stock Item: This item is not normally stocked in our distribution facility.****Technical Characteristics**

Number of Functions	1
Reset Time	50
Repeatability Constant Voltage and Temperature	1
Output Type	Electromechanical
Contact Configuration	SPDT
Timing Range	3 s to 300 s
Functions Available	On-delay
Contact Materials	AgNi
Time Scales	3 to 300sec
Shock Resistance	15 gn - 11 ms
Minimum Switching Requirement	12 V per 10
Input Voltage Range	110 to 240Vac; 24V
Frequency	50/60 Hz
Weight	108.90000000000001
Degree of Protection	IP50 (Housing) - IP20 (Terminals)
Maximum Consumption AC	0.7 VA (24 VAC) - 8.5 VA (240 VAC) - 1.8 VA (110 VAC)
Tightening Torque	4.5 to 9.9 lb-in
Indication (LED)	2
Mounting Style	Din Rail
Maximum Consumption DC	0.5 W (24 VDC)
Approvals	GL - RoHS - CE - UL - CSA
Ambient Air Temperature around the Device - Operation	-20 to 60
Ambient Air Temperature around the Device - Storage	-40 to 85
Electrical Life (UL508) Operations at Rated Current (Resistive)	100,000 operations
Mechanical Life Unpowered	20,000,000 operations
Vibration Resistance - Operational	A=0.35 mm

**Shipping and Ordering**

Category	22376 - Relays, Measurement, Type RM4, RM7, RM8 & RM9
Discount Schedule	CP2
GTIN	00785901546399
Package Quantity	10
Weight	0.24 lbs.
Availability Code	Non-Stock Item: This item is not normally stocked in our distribution facility.
Returnability	N
Country of Origin	ID

As standards, specifications, and designs change from time to time, please ask for confirmation of the information given in this document.

Generated: 09/19/2011 01:57:58