

HSS Countersink Straight Shank 3 Flutes



Taper and deburring, HSS CBN-ground with triple cutting lip.

90°

Size	Shank Diameter	Order Code	Price Each
6.3mm	5mm	483-783	
8.3mm	6mm	374-799	
10.4mm	6mm	483-795	
12.4mm	8mm	374-891	
16.5mm	8mm	483-801	
20.5mm	10mm	483-813	
25mm	10mm	483-825	

60°

485332

Size	Shank Diameter	Order Code	Price Each
8mm	6mm	136-8558	
10mm	6mm	136-8560	
12.5mm	8mm	136-8561	
16mm	10mm	136-8562	
20mm	10mm	136-8563	
25mm	10mm	136-8565	