



# Pushbutton, Single Pole




NTE Type No.	Circuitry	Action		Actuator	Diag No.
54-132	SPST	ON	OFF	Metal	S37



### Terminal Types

### Integrated Wire



## Specifications

**Current Rating:** 10A 250VAC, 8A 125VDC, 4A 250VDC, 1/3 HP 125VAC

**Dielectric Strength:** 1000V RMS (min.)

**Temperature Rating:** +149°F (+65°C) Max


**Electrical Life:** 25,000 cycles Min

**Mechanical Life:** 100,000 cycles

**Terminal Type:** Integrated Wire


**Mounting Hole:** .500 (12.7)

# Pushbutton, Single Pole



NTE Type No.	Circuitry	Action		Actuator	Diag No.
54-133	SPST	ON	OFF	Metal	S38
54-134	SPST	OFF	(ON)	Metal	S38
54-135	SPST	ON	(OFF)	Metal	S38
54-136	SPDT	ON	ON	Metal	S38

SPECIAL NOTE: ( ) = Momentary Function



## Specifications

**Current Rating:** 10A 250VAC, 15A 125VDC

**Dielectric Strength:** 1000V RMS (min.)

**Temperature Rating:** +149°F (+65°C) Max

**Electrical Life:** 15,000 cycles Min

**Mechanical Life:** 40,000 cycles

**Terminal Type:** Screw Terminals

**Mounting Hole:** .500 (12.7)