

Storage Cabinets



20702
Large

I.D. Size: 4³/₈" W
x 2" H x 5¹/₄" L




20701
Small

I.D. Size: 2¹/₈" W
x 1¹/₂" H x 5¹/₄" L

Akro-Mils' clarified polypropylene drawers are the best in the industry!

- Unbreakable
- Flexible, strong, and see-through
- Chemical-resistant

- Strong plastic cabinets organize and protect components.
- A variety of drawer configurations provide versatile storage solutions.
- Cabinets stack securely and are wall mountable.
- Dividers won't get lost – molded into cabinet back.



10116



10124



10126



10144



10164

Storage Cabinets

Model No.	Description	L	Inches W	H	L	mm W	H	Ctn. Qty.
10116	16-Drawer Cabinet	10 ⁹ / ₁₆	6 ³ / ₈	8 ¹ / ₂	268	216	162	1
10126	26-Drawer Cabinet	20	6 ³ / ₈	10 ¹ / ₂	508	263	162	1
10124	24-Drawer Cabinet	20	6 ³ / ₈	15 ¹ / ₈	508	402	162	1
10144	44-Drawer Cabinet	20	6 ³ / ₈	15 ¹ / ₈	508	402	162	1
10164	64-Drawer Cabinet	20	6 ³ / ₈	15 ¹ / ₈	508	402	162	1

16-Drawer Cabinet has 8 dividers. All other cabinets have 8 small and 4 large dividers.

Additional Dividers

Model No.	Description
40716	16-pack additional dividers for small drawers
40717	6-pack additional dividers for large drawers

Steel Storage Cabinets

Heavy-duty welded-steel frame

Durable powder coated finish



Strong, high-impact polypropylene drawers

Molded-in label holder and transparent window allow instant content identification

19-Series Heavy-Duty Cabinets

Frame: 17" wide x 11" deep x 11" high with five different drawer sizes



19228

17-Series Light-Duty Cabinets

Frame: 18" wide x 6" deep x 9¹/₂" high. Drawer depth 5¹/₂"



17018

- Two cabinets fit side by side on standard 36" wide shelving.
- Removable drawers are rust, corrosion, and dent-proof.

Steel Storage Cabinets

Model No.	Description	Drawers Per Cabinet†	Drawer Dimensions			Ctn. Qty.	Drawer Model No.	Dividers 25/Pkg. Model No.
			Inches W	Inches H	Inches D			
19-Series Heavy-Duty 17" W x 11" D x 11" H (432 x 279 x 279mm)								
19228	Storage Cabinet*	28	2 ³ / ₈	2 ¹ / ₈	10 ⁹ / ₁₆	56	20228	40228
19320	Storage Cabinet*	20	3 ³ / ₈	2 ¹ / ₈	10 ⁹ / ₁₆	81	20320	40320
19416	Storage Cabinet*	16	4	2 ¹ / ₈	10 ⁹ / ₁₆	102	20416	40416
19715	Storage Cabinet*	15	3 ³ / ₈	3 ¹ / ₈	10 ⁹ / ₁₆	81	20715	40715
19909	Storage Cabinet*	9	5 ³ / ₈	3 ¹ / ₈	10 ⁹ / ₁₆	132	20909	40909
19109	Security Cabinet w/ locking door	9	5 ³ / ₈	3 ¹ / ₈	10 ⁹ / ₁₆	132	20909	40909
17-Series Light-Duty 18" W x 6" D x 9¹/₂" H (457 x 152 x 241mm)								
17018	Storage Cabinet	18	2 ³ / ₄	2 ¹ / ₂	5 ³ / ₄	70	20902	40901
17136	Storage Cabinet	36	2 ³ / ₄	1 ¹ / ₄	5 ³ / ₄	70	20502	40501

*Available with a locking door when ordered in quantities of 50 or more.

†Two removable dividers and one label per drawer included.

Storage Cabinet Hanging Systems

Mobile Steel Cabinet Rack*

Double-sided, mobile rail rack holds 12 of the 19-Series cabinets with as many as 336 drawers. Supports up to 500 lbs.



Order These Components and Quantities

30012 Double-Sided Rail Rack – Qty: 1

30424 Mobile Kit – Qty: 1

19-Series Cabinets – Mix or Match – Qty: 12

98400 Suspension Straps (Set of 2 straps) – Qty: 12 Sets

*Assembly required



Storage-Go-Round*

Access 20 cabinets and as many as 560 drawers in less than three square feet of floor space. Holds up to 1,000 lbs. of parts.

Accommodates Akro-Mils 19-Series Steel Cabinets (sold separately).

Order These Components and Quantities

98325 Storage-Go-Round with turntable base
Assembled Storage-Go-Round stands
31" L x 31" W x 60" H
(787 x 787 x 1524 mm)

19-Series Cabinets – Mix or Match – Qty: 20

*Assembly required