

**315** **0%**  
MERCURY

SR716SW (SR67)  
Watch Battery OEM  
Swiss Made

## Technical Data Sheet


### Specifications

Chemical system	Zinc / Monovalent Silver Oxide, low drain
Nominal Voltage	1,55 V
Capacity	19 mAh, Discharge over 47 kΩ at 20°C to 1,2 V
Operating Temperature	0°C – 60°C
Self Discharge	Less than 10% per year at 20°C
Weight	~0,33 g

### Dimensions


(according IEC 60086-3)

Diameter	7,90 mm (0,311")
Height	1,65 mm (0,065")



### Discharge Curve

Constant Load	47 kΩ
Starting Drain	33,2 μA
Temperature	20°C



Information and contents in this data sheet are for reference purpose only. They do not constitute any warranty or representation and are subject to change without notice. For most current information and further details, please contact your Renata representative. For safety related information please consult the PSDS document related to that product or product family.

Rev. 315MF\_OEM.02 2010/11