



Innovative **Technology**
for a **Connected** World

2.4 GHz Wireless Serial Product CL2510



THE FASTEST WAY TO WIRELESS

Based on Laird Technologies' fifth generation 2.4GHz FHSS module, the LT2510, the CL2510 product sets the standard for industrial RF communication. Available with a RS-232 DB-9 connector and housed in a rugged enclosure, the CL2510 is an ideal choice for wireless serial communications in industrial applications. As a wireless serial bridge the CL2510 can replace thousands of feet of cable.

Optimized for point-to-point or point-to-multipoint networks and embedded with Laird Technologies' robust server-client protocol, the CL2510 permits an unlimited number of clients to synchronize to a single server for low latency communications. The server and all clients in a network can communicate with any radio in range via either addressed or broadcast packets. A simple to use Windows Configuration Utility allows customers to easily configure and test the transceivers.

With its field-proven FHSS air interface protocol, the CL2510 rejects RF noise, excels in multipath scenarios, allows for co-located systems, and provides an extremely reliable communication link. It also provides a more robust, but simpler, link than ZigBee for RF applications that do not require a mesh topology.

With a throughput of up to 280 Kb/s, CL2510 delivers speedy data rates. In addition, variable output power options (up to +17 dBm) enable communication over distances that aren't achievable with competing technologies. The radio sustains a standard asynchronous serial data stream between two or more radios out of the box.

FEATURES

Easy to Use

- Standard Male DB-9 DCE serial interface
- Standard baud rates supported from 1200 to 230,400 bps
- RF Data rates of 280kbps or 500kbps, selectable
- Advanced configuration using AT Commands

Networking and Security

- Retries and Acknowledgements
- API Commands for advanced packet addressing
- Frequency Hopping Spread Spectrum for security and interference rejection
- Customizable RF Channel, System ID and Vendor ID
- Automatic Link Synchronization
- Low Latency and high throughput

global solutions: local support™

USA: +1.800.492.2320

Europe: +44.1628.858.940

Asia: +852.2268.6567

wirelessinfo@lairdtech.com

www.lairdtech.com/wireless

SPECIFICATIONS

Parameter	
Interfaces	
Serial Interface Connector	DB-9 Male (RS-232 DCE)
RF Connector	RP-SMA Jack
Power Connector	Center Positive 2.5mm Jack.
Operational	
Network Topologies	Point to Point, Point to multipoint
Security	One byte System ID, two byte Vendor ID
Number of Hopping Channels	43 or 79, user selectable
Frequency Band	2400 MHz to 2471 MHz
RF Data Rate	280kbps or 500kbps, user selectable
RF Technology	Frequency Hopping Spread Spectrum
Output Power	50mW conducted
Maximum radiated power (EIRP)	100mW (CE), or 316mW (FCC) depending on antenna and country of use
Range (Line of Sight with 2.5dBi antenna)	Outdoor: 1.5miles (2.4km) Indoor: 790ft (240m)
Sensitivity	-98dBm at 280kbps RF Rate -94dBm at 500kbps RF Rate
Electrical/Environmental	
Supply Voltage	+6V to 30V DC
Max Power	300mW
Temperature (Operating)	-40C to 80C
Temperature (Storage)	-50C to 85C
Physical	
Dimensions	4.4 x 2.7 x 1.4 inches (11.18 x 6.86 x 3.56 cm)
Weight	6 oz (170g)
Certifications	
FCC	Yes- FCC ID: KQL-CL2510
IC	Yes: IC ID: 2268C-CL2510
CE	Yes: EN300 328-2 V1.71, EN301 489
RoHS	Yes

ORDERING INFORMATION

CL2510-100-232	2.4GHz ConnexLink 100mW RS232 Serial Transceiver
CL2510-100-232-SP	2.4GHz ConnexLink 100mW RS232 Starter Pack includes 2 units

LWS-DS-CL2510 0810

Any information furnished by Laird Technologies, Inc. and its agents is believed to be accurate and reliable. All specifications are subject to change without notice. Responsibility for the use and application of Laird Technologies materials rests with the end user, since Laird Technologies and its agents cannot be aware of all potential uses. Laird Technologies makes no warranties as to the fitness, merchantability or suitability of any Laird Technologies materials or products for any specific or general uses. Laird Technologies shall not be liable for incidental or consequential damages of any kind. All Laird Technologies products are sold pursuant to the Laird Technologies' Terms and Conditions of sale in effect from time to time, a copy of which will be furnished upon request. © Copyright 2010 Laird Technologies, Inc. All Rights Reserved. Laird, Laird Technologies, the Laird Technologies Logo, and other marks are trade marks or registered trade marks of Laird Technologies, Inc. or an affiliate company thereof. Other product or service names may be the property of third parties. Nothing herein provides a license under any Laird Technologies or any third party intellectual property rights.