




## Scatola di connessione IP68 "Paguro®" Junction box IP68 "Paguro®"



Per cavi tondi di tipo H05RN-F, H07RN-F, FG7OR, FROR

Codice 5625/08 - Ø min 6.5 - Ø max 8  
Codice 5625/10 - Ø min 7.5 - Ø max 10  
Codice 5625/12 - Ø min 9.5 - Ø max 12

### SPECIFICHE TECNICHE

- Connessione 3x4 mm<sup>2</sup>
- Tensione nominale: 400V

For round cables type H05RN-F, H07RN-F, FG7OR, FROR



Code 5625/08 - Ø min 6,5 - Ø max 8  
Code 5625/10 - Ø min 7,5 - Ø max 10  
Code 5625/12 - Ø min 9,5 - Ø max 12

### TECHNICAL DETAILS

- Connection 3x4 mm<sup>2</sup>
- Rated voltage 400V

- \* Fornito di vite autofilettante 005625/41682: Ø 4,2x16 mm e morsetteria 3x4 mm<sup>2</sup> di 005625/3/427
- \* Supplied with self threading screws 005625/41682: Ø 4,2x16 mm Terminal block 3x4 mm<sup>2</sup> 005625/3/427



## Componenti connessione Connection components



Materiale / Material

6 Nylon 66 RV

Codice / Code	Dimensioni / Dimensions (mm)				Colore / Colour		
	A	B	C	D	6 Blu Bleu	7 Verde Green	9 Giallo Yellow
5625/08	95	45	24	8	Materiale / Material →		6
5625/10	95	45	24	10		6	
5625/12	95	45	24	12	6		



Materiale / Material

6 Nylon 66 RV

Codice / Code	Dimensioni / Dimensions (mm)				Colore / Colour	
	A	B	C	E	0 Neutro Natural	6
005625/3/427	31,5	23	20,7	12	Materiale / Material →	6

Esempio di montaggio "Paguro®"  
Assembly's example "Paguro®"

