

HP2050

Max in masonry	H: 13, L: 20 mm
Max in steel	H: 8, L: 13 mm
Max in wood	H:25 & L:40 mm
Blows per minute	H: 0-58000/ L: -24000 bpm
Vibration drilling	2.5 m/sec ²
Vibration hammer drilling	13 m/sec ²
No load speed	H: 0 - 2900 / L: 0 - 1200 rpm
Input wattage	720 w
Vibration K factor	3 m/sec ²
Noise sound power	108 dB(A)
Noise sound pressure	97 dB(A)
Noise K factor	3 dB(A)
Net weight	2.3 kg



STANDARD EQUIPMENT: 824650-5 CARRYING CASES FOR MAINS MACHINES - PLASTIC