

a vital part of your world

Text Search:

Thursday, 24 November, 2005

CATALOG

 → [Cross Reference](#)
[Competitive Products](#)
[Military Spec P/Ns](#)
[Tyco Brand P/Ns](#)

- [Part Number Search](#)
- [Document Search](#)
- [Product Type Search](#)
- [Product Family Search](#)
- [Alphabetical Search](#)
- [RoHS/ELV Compliance & Alternates](#)
- [CAD Model Search](#)
- [Brand Search](#)
- [Tool Search](#)
- [Multiple Part Comparison](#)
- [Lead Free Solutions](#)
- [Help/Glossary](#)

[Home](#)

 e-bulletin newsletter
SUBSCRIBE NOW!
 click here

Soft Shell Connectors
↳ .163" Centerline, 600 V, 9.5 A max. (Mini Universal MATE-N-LOK)
AMP 171639-1 [Active](#)
Directive 2002/95/EC
Compliant
[RoHS Compliant](#)
(Corporate P/N: 171639-1)
[Search for Parts](#)

Document links for this part cannot be displayed. Your browser does not support inline frames or is currently configured not to display inline frames. Inline frames are supported in both Internet Explorer 5 and Netscape 6, as well as all later versions of these browsers.

Related Part Information

General Information	eCommerce	Related Part Information
<ul style="list-style-type: none"> ➤ General Info ➤ Sales Info ➤ Assembly Subcontractors 	<ul style="list-style-type: none"> ➤ Pricing & Availability 	<ul style="list-style-type: none"> ➤ Tooling

Photos & Line Drawings - The photographs and/or line drawings are representative images of a product for viewing purposes only.

[Product Photo](#)
Searchable Features:

Brand:	AMP
RoHS/ELV Compliance:	RoHS compliant, ELV compliant
Lead Free Solder Processes:	Not relevant for lead free process
Product Type:	Contact
Connector Line:	Mini-Universal MATE-N-LOK
Gender:	Socket
Packaging Method:	Loose Piece
Wire Range (mm [AWG]):	0.50-1.25 ² [20-16], (2) 0.50 ² [20]
Contact Material:	Brass
Wire Insulation Diameter (mm [in]):	2.01 – 3.20 [0.079 – 0.126], 2.40 [0.094]
Contact Termination Area Plating:	Pre-Tin

Other Properties:

RoHS/ELV Compliance History:	Always was RoHS compliant
Contact Diameter (mm [in]):	0.99 [0.039]
Stock Thickness (mm [in]):	0.20 [0.008]
Voltage (VAC):	600
Current Rating (Amps.):	9.5
CompactPCI:	No

[Copyright and Privacy Statement](#)
 Visit [Tyco International Ltd.](#)