

DYMO**LabelManager****500TS**

Touch Screen Label Maker with PC or Mac® Connection



The first standalone office touch screen label maker from DYMO.


Name anything you ever wanted to do with a label maker—the revolutionary DYMO Touch Screen™ label maker lets you do it with ease! Edit, format, and customize labels with a touch of your fingertip. Connect to your PC or Mac®* and use DYMO Label™ software to customize your labels with fonts or graphics—even download your labels for editing and printing on the go.

LabelManager® 500TS Features

- 1 Large, full-color touch screen – a DYMO first! Just tap to create, edit and format labels with ease
- 2 Speed text entry using the computer-style keyboard
- 3 Eliminate the hassle of manual cutting with an automatic label cutter
- 4 Customize your labels with 10 fonts, 25 font sizes, 5 boxes plus underline, 32 text styles and 325 built-in symbols and clip art images
- 5 Prints crystal clear graphics, barcodes and logos at 300 dpi resolution
- 6 Share without losing your settings—new user profiles let you store settings and data for up to 5 different users
- 7 Avoid the cost and waste of disposable batteries with the rechargeable battery pack
- 8 Label fast—prints twice as fast as other DYMO label makers



Rechargeable
Battery Pack



Connect to your PC or Mac®* and use DYMO Label™ software to customize your labels with fonts or graphics—even download your labels for editing and printing on the go

DYMO Label™ Software



Custom fonts and graphics Works with any fonts or graphics on your computer – customize with your company logo and much more!

Multi-application Print labels from within Microsoft® Word, Excel® or Outlook®, Mac® Address Book, QuickBooks® and other programs

PC or Mac® Works with Windows® XP, Windows Vista®, Windows® 7 or Mac OS® v10.4 or later

* Compatible with Microsoft® Windows® XP, Windows Vista®, Windows® 7 or Mac OS® v10.4 or later



www.dymo.com



D1 Labels

Standard, Permanent or Flexible...
Depend on durable DYMO labels.



Standard labels for hundreds of tasks around the office or home office, such as filing, storage, asset management, and reminders. Available in continuous label cassettes, you can create sharp, easy-to-read labels of just about any length.



Permanent labels look the same as standard labels but offer a powerful, permanent adhesive for when you want a label to stay put indefinitely.



Flexible labels are for curved and/or heavily textured surfaces and flag-marking cables. Its permanent adhesive means it will stay put.



Easy Peel



UV Resistant



Water Resistant



Temperature: 0°F-194°F

LabelManager® 500TS Specifications

Item #1790417 List Price \$279.99

LabelManager® 500TS Pack Content

- Electronic label maker
- D1 starter label cassette, black on white, 1" x 10'
- Rechargeable battery pack
- Charging adapter
- USB cable
- Quick Start and Reference Guides
- 1-Year Limited Warranty Card

LM500TS Pack Unit

| | |
|--------------|--------|
| Length | 9.31" |
| Width | 12.25" |
| Height | 5.00" |
| Weight (lbs) | 2.43 |

Shipper

| | |
|-------------------|--------|
| Length | 19.50" |
| Width | 15.75" |
| Height | 13.50" |
| Weight (lbs) | 16.32 |
| Units per Shipper | 6 |

D1 labels for the LabelManager® 500TS

Standard (available in 1/4", 3/8", 1/2", 3/4" and 1" X 23") List Price: **\$19.67** (1/4", 3/8" and 1/2") **\$27.43** (3/4" and 1")

| | BLACK•WHITE | RED•WHITE | BLACK•YELLOW | BLACK•RED | BLACK•CLEAR | RED•CLEAR |
|------|-------------|-----------|--------------|-----------|-------------|-----------|
| 1/4" | 43613 | - | - | - | 43610 | - |
| 3/8" | 41913 | 40915 | - | - | 40910 | - |
| 1/2" | 45013 | 45015 | 45018 | 45017 | 45010 | 45012 |
| 3/4" | 45803 | 45805 | 45808 | 45807 | 45800 | - |
| 1" | 53713 | - | - | - | 53710 | - |

| | BLUE•WHITE | WHITE•BLACK | BLACK•BLUE | BLACK•GREEN | WHITE•CLEAR | BLUE•CLEAR |
|------|------------|-------------|------------|-------------|-------------|------------|
| 1/4" | - | - | - | - | - | - |
| 3/8" | 40914 | - | - | - | - | - |
| 1/2" | 45014 | 45021 | 45016 | 45019 | 45020 | 45011 |
| 3/4" | 45804 | 45811 | 45806 | 45809 | - | - |
| 1" | - | - | - | - | - | - |



Flexible (available in 1/2" and 3/4" x 11.5")
List Price: **\$19.00** (1/2") **\$26.50** (3/4")

| | BLACK•WHITE |
|------|-------------|
| 1/2" | 16953 |
| 3/4" | 16954 |

Permanent (available in 1/2" and 3/4" x 18")
List Price: **\$19.00** (1/2") **\$26.50** (3/4")

| | BLACK•WHITE |
|------|-------------|
| 1/2" | 16955 |
| 3/4" | 16956 |

Labels are available through many office and computer catalogs, superstores and online resellers. For a complete listing of available labels, visit www.dymo.com. DYMO, the DYMO logo, and LabelManager are trademarks or registered trademarks of Sanford, L.P. or its affiliates. All other trademarks are the property of their respective owners. Microsoft Windows, Windows Vista, the Windows logo, Outlook and Excel are trademarks or registered trademarks of Microsoft Corporation. Mac and MacOS are registered trademarks of Apple, Inc. All other trademarks are the property of their respective owners. All individual company names used on sample labels are fictitious.



Distributed by:
DYMO, Atlanta, GA 30328
800-426-7827
www.dymo.com
©2011 Sanford, L.P.
11-0110 S4410

www.dymo.com