


Item no.: 273-100
 Product description: Push-wire connector for junction boxes 3-conductor terminal blocks



Produkt kann von Bild abweichen / product may differ

Packing unit 1000 10*100 pieces

RoHS compliant

Product group	7 (Push Wire Conn.)
pole count	3
Cross section [mm ²]	0.75 - 1.5 mm ²
Cross section [AWG]	18 - 16 AWG
Wiring method	e
Connection method	PUSH WIRE®
Measured voltage EN	400 V
Measured shock voltage	4 kV
Pollution degree	2
Current intensity EN	18 A
Weight	1.9 g
Color	grey
Wiring type	Side-entry
No. of connection Points	3
No. of potentials	1
Height	8.6 mm
Height	0.339 in
Width	11.5 mm
Width	0.453 in

Depth	18 mm
Depth	0.709 in
Strip length from	10 mm
Strip length to	13 mm
Strip length	0.45 in



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
273-100	ABS	10-HN17750340X	400	24	1,5
273-100	BV	11941/BO	400	17,5	1,5
273-100	CCA	DK2515	400	17,5	1,5
273-100	CSA	154112-1059435	600	10	20-16
273-100	DEMKO	40677-02	400	17,5	1,5
273-100	DNV	E-9215	400	18	1,5
273-100	FIMKO	FI24029	400	17,5	1,5
273-100	GL	17294-00HH	400	17,5	1,5
273-100	LR	04/20013(E3)	400	17,5	1,5
273-100	NEMKO	P08108775	400	17,5	1,5
273-100	ÖVE	1193-033-05	400	17,5	1,5
273-100	RosTest	AB24 B04007			
273-100	SEMKO	99-00683	400	17,5	1,5
273-100	SEV	10.0146	400	17,5	1,5
273-100	UL listed	E69654	600	20	20-16
273-100	VDE	40024009	400	17,5	1,5

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected