



# Fixed Wallplate 2 Port PowerCat UTP/FTP Category 5E

**Features and Benefits**

The PowerCat 2 Port Shuttered Fixed Wallplate offers an economic alternative to the modular system, eliminating the need for separate components as only one part is needed. The Wallplate is a complete assembly, comprising 2, C5E RJLP Connectors, Fascia, Spring Loaded Shutters and a protected labelling facility. The product is designed to be compatible with UK single gang back boxes.

Molex Premise Networks unique patented RJLP RJ45 Connector is engineered to meet the highest performance standards in the industry and offers a low profile, space saving design, that allows installation in shallow back boxes and trunking.

Suitable for high speed data transmission, the PowerCat RJLP RJ45 was designed to meet the requirements of the C5E standard which demands compliance with the PowerSum principle of measurement and test.

- UK standard 86 x 86 mm fascia
- Low Profile Cat 5E RJ45 Connectors
- Spring loaded shutters
- FTP version provides through-shield continuity

**Technical Specification**

**Termination Tools:**

Molex and industry standard tooling

**IDC Terminations:**

Suitable for 0.4mm - 0.6mm solid or stranded cable, maximum o.d. 1.5mm. Two wires may be terminated for daisy-chain applications.

**Mechanical**

**Jack Connector**


Operating Life : Minimum 500 insertion cycles  
 Contact Material : Phosphor Bronze  
 Contact Plating : 1.25 micrometres Au/Ni  
 Material : UL 94V0 Thermoplastic

**IDC Connector**

Operating Life : Minimum 100 Reterminations  
 Contact Material : Phosphor Bronze  
 Contact Plating : Sn/Pb over Ni  
 Wire Size : 2x26-22 AWG solid or stranded

**Electrical**

D.C. Resistance : <20 mΩ  
 D.C. Resistance Imbalance : <2.0 mΩ  
 Insulation Resistance : >100 MΩ  
 Attenuation (dB) @ 1MHz 0.0121  
 @ 16MHz 0.0193  
 @ 100MHz 0.1052  
 Crosstalk(dB) @ 1MHz -84.26  
 @ 16MHz -60.03  
 @ 100MHz -45.70  
 PowerSum Worst Pair (dB) @ 100MHz -41.83  
 Return Loss (dB) @ 1MHz -65.0  
 @ 16MHz -48.0  
 @ 100MHz -30.0



Order No.	Description
WNC-00008-02	2 Port PowerCat Fixed Shuttered UTP Wallplate 568B Category 5E, White
WNC-00011-02	2 Port PowerCat Fixed Shuttered FTP Wallplate 568B Category 5E, White

**MOLEX PREMISE NETWORKS**

Molex Premise Networks  
 Corporate Headquarters  
 Tel: 603 324 0200  
 www.molexpn.com

Western Europe Headquarters  
 Tel: 44 (0) 1489 572111  
 www.molexpn.co.uk

Eastern Europe Headquarters  
 Tel: 48 22 36 92 51  
 www.molexpn.com.pl

Asia Headquarters  
 Tel: 852 2637 3759  
 www.molexpn.com.hk

South Pacific Headquarters  
 Tel: 61 3 9747 8322  
 www.molexpn.com.au

Molex Incorporated  
 Tel: 630 969 4550  
 www.molex.com