



**Pressure switches for mounting on plan 25x32 Positive output Part number 81505150**


■ xxx

	Type	Setting range
81505140	Positive output	50 →500 mb
81505150	Positive output	0,1 →2,5 b
81505160	Positive output	2 →8 b
81502140	Negative output	50 →500 mb
81502150	Negative output	0,1 →2,5 b
81502160	Negative output	2 →8 b

**Symbol**


Orifice diameter mm	2,5
Flow at 4 bars NI/min	170
Hysteresis 50→500 mb	60 mb
Hysteresis 0,1→2,5 b	100 mb
Hysteresis 2→8 b	320 mb
Connection - Sub-base	■
Operating temperature (° C)	-5 + 50
Mechanical life (operations)	3.10 <sup>6</sup>
Weight (g)	160
Accuracy 0,1→2,5 mb	10%
Accuracy 2→8 b	4%
Accuracy 50→500 mb	4%

**Dimension Diagram : \*\*\* TRADUCTION MANQUANTE \*\*\***

**: \*\*\* TRADUCTION MANQUANTE \*\*\***


\*\*\* TRADUCTION MANQUANTE \*\*\*

N°	Legend
----	--------

**Curves : \*\*\* TRADUCTION MANQUANTE \*\*\***



N° Legend

- 1
- 2
- 3
- 4
- 5

: \*\*\* TRADUCTION MANQUANTE \*\*\*

