

[How to Order](#)[View Product List](#)[Help](#)[Catalog Login](#)[Find A Product](#)

Search by Part or UPC Number in:

Entire Catalog Begins With ... **-OR-**Search Entire Catalog  
Using Keywords:[Return to Previous Page](#)**Quicklag Industrial Circuit Breaker**[Click for larger image](#)

(Actual product appearance may differ from product shown)

**Related Information**[Product information, manuals and drawings.](#)**Miniature Industrial Circuit Breaker, Type BAB, Bolt-on, 3-Poles, 30 AMP, 240 V/ Ring or Spade Lug Terminals**Add Quantity  To Product List 

Catalog Number:	BAB3030HT
Style Number:	7804C04G04
UPC Number:	00786679377925
Product Code:	3703C
List Price:	\$257.00
Order in Multiples of:	1
Usually Ships:	Same Day
Weight:	.88 lbs
Dimensions:	3.25 in x 3 in x 3.5 in
Regulatory Compliance:	UL and CSA Listed
Warranty Information:	1 Year
Circuit Breaker Type:	BAB
Trip Style:	Thermal-Magnetic, Fixed
Connection Type:	Bolt-on
Number of Poles:	3
Continuous Ampere Rating at 40 degrees C (AMP):	30
Voltage Rating (VAC):	240
Interrupting Capacity (kAIC):	10
Options:	Ring or Spade Lug Terminals
Catalog Notes:	

[Privacy Policy](#) | [How Can We Improve This Page?](#) | [Terms & Conditions](#)Copyright © ,2003 Eaton Corporation,  
All Rights Reserved