


## PRODUCT DATA

### Magnet Thermocouple, Type K



- Strong magnet housing type K thermocouple
- 2 metres stainless steel over-braided PFA Teflon® cable fitted with miniature plug
- Temperature rating -50°C to +250°C
- Rapid, reliable temperature sensing on ferrous surfaces
- Grounded measuring junction

### Specifications

Sensor type:	Type K thermocouple to IEC 584
Construction:	Thermo-element located in 1" diameter magnet
Cable/Termination:	2 metres PFA Teflon® insulated with stainless steel over-braid, miniature plug termination
Thermocouple junction:	Grounded at tip
Magnet:	1" diameter (3kg pull)
Temperature range:	-50°C to + 350°C

### Code:

Labfacility code	Stock code	Farnell code
BMS-K-2-C70-MP (1" magnet)	XF-581-FAR	NEW