



Workshop vernier caliper 805.M by Facom, with capacity from 1 to 200 mm. Measurement inside and outside. Resolution 0,02 mm. Bias error 30  $\mu\text{m}$ . Vernier with thumb positioning guide. Minimum vernier life expectancy 20,000 cycles. Minimum rule hardness 40 HRc. Length of the tool 290 mm. Standard DIN 863. Digital calipers 805.M is with lifetime guarantee. Measurement tool from hand tools manufacturer Facom.

<input type="checkbox"/>	Capacity	200 mm
<input type="checkbox"/>	Resolution	0.02 mm
<input type="checkbox"/>	Bias error	30 $\mu\text{m}$
<input type="checkbox"/>	Length	290 mm
<input type="checkbox"/>	Measurement	inside, outside
<input type="checkbox"/>	Class	0
<input type="checkbox"/>	Standard	metric
<input type="checkbox"/>	mm/inch conversion	no
<input type="checkbox"/>	Software	no
<input type="checkbox"/>	Weight	0.423 kg
<input type="checkbox"/>	Guarantee	lifetime
<input type="checkbox"/>	Standards	DIN 863