

Product finder: [Home](#)

FILTERED SEARCH

- Manufacturer
(choose) *
- LED
(choose) *
- Diameter
(choose) *
- Height
(choose) *
- Viewing Angle (FWHM)
(choose) *
- Family
(choose) *
- Material
(choose) *
- Type of Optics
(choose) *
- Single vs Multi Optics
(choose) *

[Show 2212 hits](#)

Ledil Oy
Salorankatu 10
FI-24240 SALO
Finland
VAT FI17894629

If you have any question
for Sales, please contact
us.

[Logistics, Shipping and
Terms](#)
[Careers](#)

CN12160_LENA-W-DL

DETAILS

Ordering Number	CN12160_LENA-W-DL
Family	Lena
Type	Reflector
LED	BXRA-C0800/1200/2000
Color	Metal
Diameter	111 mm
Height	87.8 mm
Style	Round
Optic Material	PMMAPC
Holder Material	PC
Fastening	Screw
Status	In Production
ROHS compliant	yes
Date Updated	23/11/2011

OPTICAL PROPERTIES

Viewing Angle (FWHM)	46°
Light Beam Type	Wide
Efficiency	-
cd/lm	-

GENERAL INFORMATION

Materials	PMMA 8N UL 94
	PMMA 8N Plexiglas
	PC Makrolon datasheet
	PC Makrolon UL

Installation

CONTACT US

Didn't find what you were looking for? Please Contact Us!

[<< back to search results](#)[PRODUCT DATASHEET](#)[MECHANICAL
DRAWING](#)[REQUEST 3D
MECHANICAL MODEL](#)[REQUEST
PHOTOMETRIC FILES](#)