



Product finder:

Home
FILTERED SEARCH

- Manufacturer *
- LED *
- Diameter *
- Height *
- Viewing Angle (FWHM) *
- Family *
- Material *
- Type of Optics *
- Single vs Multi Optics *

Show 2212 hits

Ledil Oy
Salorankatu 10
FI-24240 SALO
Finland
VAT FI17894629

If you have any question
for Sales, please contact
us.

Logistics, Shipping and
Terms
Careers

CN12168_LENA-M-DL

DETAILS

Ordering Number	CN12168_LENA-M-DL
Family	Lena
Type	Reflector
LED	BXRA-C0800/1200/2000
Color	Metal
Diameter	111 mm
Height	87.8 mm
Style	Round
Optic Material	PMMAPC
Holder Material	PC
Fastening	Screw
Status	In Production
ROHS compliant	yes
Date Updated	23/11/2011

OPTICAL PROPERTIES

Viewing Angle (FWHM)	20°
Light Beam Type	Medium
Efficiency	-
cd/lm	-


GENERAL INFORMATION

- Materials**
- PMMA 8N UL 94
 - PMMA 8N Plexiglas
 - PC Makrolon datasheet
 - PC Makrolon UL

Installation

CONTACT US

Didn't find what you were looking for? Please Contact Us!



<< back to search results

- PRODUCT DATASHEET
- MECHANICAL DRAWING
- REQUEST 3D MECHANICAL MODEL
- REQUEST PHOTOMETRIC FILES

