


Bits and Sleeves



Standard Wrap



Modified Wrap

All bits and sleeves listed below fit the universal collet as fitted to the tools opposite.

Wire Size AWG	Terminal Min.	Diagonal Max.	Terminal Hole Depth	BIT		SLEEVE	
				Mftrs. List No.	Order Code	Mftrs. List No.	Order Code
Standard Wrap							
22	1.55	2.18	25.4	18632	147-841	18840	147-842
24	1.4	1.88	25.4	512058	147-845	512056	147-846
26	1.47	1.88	25.4	504910	147-847	512056	147-846
Modified wrap							
24	1.33	1.88	28.8	26263	147-848	18840	147-842
26	0.58	0.99	19.1	506445	147-849	507100	147-850
26	1.35	1.75	25.4	502118	147-851	512056	147-846
30	0.79	0.86	19.1	507063	147-853	507100	147-850
30	0.84	0.91	19.1	507573	147-854	507100	147-850
Cut Strip and Wrap							
30	0.76	0.86	25.4	990764	109-261	990765	109-365

222653,401577

	BITS		SLEEVES	
	Order Code	Price Each	Order Code	Price Each
Standard Wrap				
22AWG	147-841		147-842	
24AWG	147-845		147-846	
26AWG	147-847		147-846	
Modified Wrap				
24AWG	147-848		147-842	
26AWG	147-849		147-850	
26AWG	147-851		147-846	
30AWG	147-853		147-850	
30AWG	147-854		147-850	
Cut Strip and Wrap				
30AWG	109-261		109-365	