









## Miniatur Rundsteckverbinder Serie 680 Miniature circular connectors series 680

## Kabelsteckverbinder Cable connectors

Bezeichnung – Abbildung Description – Figure	Maßzeichnung Drawing	Polzahl Contacts	Bestell-Nr./Ordering-No.	
			versilberte Kontakte silver plated contacts	vergoldete Kontakte gold plated contacts
Kabelstecker Kabeldurchlass 3 - 6 mm <i>Cable connector            cable outlet 3 - 6 mm (.12 - .24 in.)</i> 		2	09-0301-00-02	09-0301-09-02
		3 DIN	09-0305-00-03	09-0305-09-03
		4	09-0309-00-04	09-0309-09-04
		5	09-0313-00-05	09-0313-09-05
		5 (Stereo)	09-0317-00-05	09-0317-09-05
		6 DIN	09-0321-00-06	09-0321-09-06
		7	09-0325-00-07	09-0325-09-07
		7 DIN	09-1581-00-07	–
		8 DIN	09-0571-00-08	09-0571-09-08
		12	–	09-0329-00-12
		14	–	09-0341-00-14
		16	–	09-0337-00-16
		19	–	09-0343-00-19
		24	–	–
Kabelstecker Kabeldurchlass 6 - 8 mm <i>Male cable connector            cable outlet 6 - 8 mm (.24 - .32 in.)</i> 		2	09-0301-02-02	09-0301-92-02
		3 DIN	09-0305-02-03	09-0305-92-03
		4	09-0309-02-04	09-0309-92-04
		5	09-0313-02-05	09-0313-92-05
		5 (Stereo)	09-0317-02-05	09-0317-92-05
		6 DIN	09-0321-02-06	09-0321-92-06
		7	09-0325-02-07	09-0325-92-07
		7 DIN	–	–
		8 DIN	09-0571-02-08	09-0571-92-08
		12	–	09-0329-02-12
		14	–	09-0341-02-14
		16	–	09-0337-02-16
		19	–	09-0343-02-19
		24	–	09-0345-02-24
Kabeldose Kabeldurchlass 3 - 6 mm <i>Female cable connector            cable outlet 3 - 6 mm (.12 - .24 in.)</i> 		2	09-0302-00-02	09-0302-09-02
		3 DIN	09-0306-00-03	09-0306-09-03
		4	09-0310-00-04	09-0310-09-04
		5	09-0314-00-05	09-0314-09-05
		5 (Stereo)	09-0318-00-05	09-0318-09-05
		6 DIN	09-0322-00-06	09-0322-09-06
		7	09-0326-00-07	09-0326-09-07
		7 DIN	09-1582-00-07	–
		8 DIN	09-0572-00-08	09-0572-09-08
		12	–	09-0330-00-12
		14	–	09-0342-00-14
		16	–	09-0338-00-16
		19	–	09-0344-00-19
		24	–	–
Kabeldose Kabeldurchlass 6 - 8 mm <i>Male cable connector            cable outlet 6 - 8 mm (.24 - .32 in.)</i> 		2	09-0302-02-02	09-0302-92-02
		3 DIN	09-0306-02-03	09-0306-92-03
		4	09-0310-02-04	09-0310-92-04
		5	09-0314-02-05	09-0314-92-05
		5 (Stereo)	09-0318-02-05	09-0318-92-05
		6 DIN	09-0322-02-06	09-0322-92-06
		7	09-0326-02-07	09-0326-92-07
		7 DIN	–	–
		8 DIN	09-0572-02-08	09-0572-92-08
		12	–	09-0330-02-12
		14	–	09-0342-02-14
		16	–	09-0338-02-16
		19	–	09-0344-02-19
		24	–	09-0346-02-24