



Interface Solutions UK Ltd.

www.interfacesolutions.uk.com

1 Fontwell Road
 Little Lever
 Bolton
 Lancashire
 BL3 1TE

Tel/Fax: 01204 708302
 tech@interfacesolutions.uk.com

(IS TR) **Toggle Relay**

The toggled relay is a simple low cost module ideal for use with radio controlled transmitter receivers to operate gates, doors, barriers, CCTV cameras and alarm systems. It has been designed for 12 or 24 Volt DC operation and has a double pole relay rated at 8 amps 240 V AC complete with LED indication.

Operation:

The relay is activated by a trigger which can be a positive or negative voltage applied or removed from the 'T' terminal. This gives a toggled on-off action.

Options:

LINK IN	TRIGGER	RELAY
A	Applied	Not latched
B	Removed	Not latched
C	Removed	Latched
D	Applied	Latched

Supply Voltage	12 Volts DC	24 Volts DC
Quiescent Current	8 mAmps	23 mAmps
Current when active	38 mAmps	68 mAmps
Double Pole Relay rated at	8 Amps at 240 V AC	
Dimensions	57mm (W), 82mm (L), 20mm (H)	

We recommend IS Sticky feet size B, self-adhesive mounting pillars to ensure a neat fixing

