

TENMA®



Multiple Outlet DC Power Strip

This "must-have" is essential for any benchtop where several items are connected to a single power supply. It is especially convenient when a number of permanent items are connected, while others are routinely added and removed. Color coded binding posts accept spade terminals, bare wire, single or paired banana plugs. This unit is divided into two independent sections, with a combined total current capacity of 35A.

Section One

- Two sets of heavy duty, individually fused binding posts, current capacity 35A each, total max combined capacity 35A
- 0~35A analog ammeter
- LED status indicator

Section Two:

- Six sets of 10A binding posts, 15A max total capacity
- 15A fuse for entire set
- 0~15A analog ammeter
- Rocker switch with LED status indicator

Other Features

- Isolated steel case
- Separate ground lug
- Attached 6' lead with color-coded, gold plated spade lugs
- Mounting hole centers 12-1/2"
- Dimensions: 2-1/2" (H) x 3-1/2" (W) x 13" (L) including binding posts

Order # 72-6627
MCM an InOne company
www.mcminone.com