

Steel Alligator Clip w/Barrel & Screw, 10 Amp

Features

- Nickel Plated
- Screw Connection
- Overall Length: 1.950" (49.5mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-153	Steel Alligator Clip with Barrel & Screw



72-153 Series Kit

Features

- 10 Amp Steel Alligator Clip w/Barrel & Screw
- Flexible PVC Composition Insulator

NTE Type No.	Kit Contains
72-153-KIT	2 Pair of 72-153 Steel Alligator Clips 2 Pieces of 72-157-0 Black Insulators 2 Pieces of 72-157-2 Red Insulators



Solid Copper Alligator Clip w/Barrel & Screw, 10 Amp

Features

- Screw Connection
- Overall Length: 1.950" (49.5mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-151	Solid Copper Alligator Clip with Barrel & Screw



72-151 Series Kit

Features

- 10 Amp Solid Copper Alligator Clip w/Barrel & Screw
- Flexible PVC Composition Insulator

NTE Type No.	Kit Contains
72-151-KIT	2 Pair of 72-151 Solid Copper Alligator Clips 2 Pieces of 72-157-0 Black Insulators 2 Pieces of 72-157-2 Red Insulators



Steel Alligator Clip w/Threaded Barrel, 10 Amp

Features

- Nickel Plated
- 8-32 UNC Threaded Barrel Connection
- Overall Length: 2.125" (53.9mm)
- Jaw Opening: .310" (7.87mm)

NTE Type No.	Description
72-154	Steel Alligator Clip with Threaded Barrel

