



## 4600 Staticide® Ultra Floor Finish

### High Quality, High Performance

No other ESD floor finish can match Staticide® Ultra Floor Finish for electrical properties, physical longevity, and gloss. This urethane-enhanced formula features superior abrasion resistance and durability, fortifying floors with a long-lasting protective layer that is shiny and ESD-safe for 12 to 24 months.

By maximizing stripping cycles, companies can keep costs down by eliminating annual labor fees and production shut-downs.

Staticide® Ultra Floor Finish is the perfect choice for any environment where static control is required, such as electronic, medical, and clean room manufacturing facilities. With an average surface resistivity of  $10^8$  -  $10^9$  ohms per square, Staticide® Ultra Floor Finish fulfills ANSI/ESD S20.20 guidelines and is suitable for sensitive device manufacturing.

This water-based formula is UL listed for slip resistance, RoHS compliant, biodegradable, non-flammable, and free of formaldehyde, phthalates, alkalis, acids, and ammonia.

**Directions:** Clean floor and apply two thin coats of floor finish with a dedicated rayon mop. Wait one hour between coats. Consult application procedure for details and precise instructions.

**Maintenance:** Sweep or damp mop daily to remove dirt. Periodically clean with a 1:1 dilution of water and floor finish. Apply a thin top coat of floor finish every 4 – 6 weeks. For heavy cleaning, use the 4100 Restorer Cleaner. Consult maintenance procedure for details and precise instructions.

*Product #4600-1; 4 gallons per case  
Product #4600-5; 5-gallon pail  
Product #4600-2; 54-gallon drum*

- ❖ **Coverage: 1,500 - 2,000 square feet per gallon**
- ❖ **Non-toxic; biodegradable**
- ❖ **Solids: 20 ± 5%**
- ❖ **Strip cycle: 12-24 months**
- ❖ **Suitable to use on vinyl, linoleum, and ceramic tile**
- ❖ **Surface resistivity:  $10^8$  –  $10^9$  ohms per square (average)**
- ❖ **Low V.O.C.**
- ❖ **Water-based polyurethane**

